



Cable ties for food industry, detectable, corrosion resistant

MCTS-Series, PA66MP+

Our MCTS cable ties have been specifically developed to be used in the food and beverage as well as in the pharmaceutical industry. A unique manufacturing process in combination with a unique material formulation offers outstanding performance in line with high corrosion resistance. This makes the MCTS an ideal product even for very humid environments. In addition, the MCTS ties manufactured from a polypropylene base material offer very good chemical resistance.

Features and benefits


- Total metal dispersion throughout the tie
- Can support quality assurance in the production of food stuffs, for example HACCP
- Blue colour for easy visual detection
- Greatly reduces risk of contamination
- Magnetic detectable (detection level depending on specific application and equipment)
- MCTS ties have very good corrosion resistance



Our detectable MCT(S) cable ties are used in the food and pharmaceutical industry.

i More colours on request. Please contact us.

i Can support quality assurance in the production of food stuffs, for example HACCP.



TYPE	Width (W)	Length (L)	Bundle Ø max.	N	Material	Colour	Pack Cont.	Tools	Article-No.
MCTS100	2.5	100.0	22.0	60	PA66MP+	Blue (BU)	100 pcs.	2;5-6	111-01341
	2.5	100.0	22.0	60	PA66MP+	Mint Green (MGN)	100 pcs.	2;5-6	111-01377
	2.5	100.0	22.0	60	PA66MP+	Mustard (MST)	100 pcs.	2;5-6	111-01380
	2.5	100.0	22.0	60	PA66MP+	Russet (RUS)	100 pcs.	2;5-6	111-01383
MCTS150	3.5	153.0	36.0	110	PA66MP+	Blue (BU)	100 pcs.	2;5-6	111-01342
	3.5	153.0	36.0	110	PA66MP+	Mint Green (MGN)	100 pcs.	2;5-6	111-01378
	3.5	153.0	36.0	110	PA66MP+	Mustard (MST)	100 pcs.	2;5-6	111-01381
	3.5	153.0	36.0	110	PA66MP+	Russet (RUS)	100 pcs.	2;5-6	111-01384
MCTS200	4.7	202.0	50.0	150	PA66MP+	Blue (BU)	100 pcs.	2-3;5-6;8;10	111-01343
	4.7	202.0	50.0	150	PA66MP+	Mint Green (MGN)	100 pcs.	2-3;5-6;8;10	111-01379
	4.7	202.0	50.0	150	PA66MP+	Mustard (MST)	100 pcs.	2-3;5-6;8;10	111-01382
	4.7	202.0	50.0	150	PA66MP+	Russet (RUS)	100 pcs.	2-3;5-6;8;10	111-01385
MCTS300	4.8	301.0	80.0	150	PA66MP+	Blue (BU)	100 pcs.	2-3;5-6;8;10	111-01399
	4.8	301.0	80.0	150	PA66MP+	Mint Green (MGN)	100 pcs.	2-3;5-6;8;10	111-01400
	4.8	301.0	80.0	150	PA66MP+	Mustard (MST)	100 pcs.	2-3;5-6;8;10	111-01401
	4.8	301.0	80.0	150	PA66MP+	Russet (RUS)	100 pcs.	2-3;5-6;8;10	111-01402

All dimensions in mm. Subject to technical changes.
Minimum Order Quantity (MOQ) may differ from package content. Other packaging options may also be available.

Recommended Tools						
	2	3	5	6	8	10
	MK20	MK21	MK3PNP2	EVO7	MK7P	EVO9
	549	549	550	552	554	553

For more information on toolings please refer to the Application Tooling chapter.



Add items to your watchlist!

www.HT.click/9-59

