

HONEYWELL UVEX A700 SERIES

The lightweight wraparound 9-base lens design provides substantial coverage and a distortion-free 180° field of vision, while the universal nose bridge and soft temple tips provide a comfortable fit. Available in a wide selection of tints to meet a variety of indoor and outdoor work applications. Clear and Gray lens options are available with Uvextra® Fog-Resistant coating for humid conditions.



A700



A703



A701



A704

FEATURES AND BENEFITS

- Sport-inspired shaping provides a stylish fit for the everyday worker
- Lightweight, flexible temples with padded tips provide a secure, wraparound fit and all-day comfort
- Molded universal nose bridge provides a comfortable fit
- 9-base polycarbonate hardcoated lens provides a 180° field of distortion-free vision
- Provides >99.9% UV protection
- Meets ANSI Z87.1 and is CSA Z94.3 certified