




제품 설명

재질

- 스틸, 경화처리 하지 않음, 흑색처리
- 스테인레스 스틸 1.4305

그림

접시 머리 스크류용 DIN EN ISO 2009
혹은 DIN EN 10642



주문 정보

d ₁	치수 d ₂ [mm]	s	[g]	부품번호.	
				스틸	스테인레스 스틸
16	4,5	3,0	3,6	22270.0016	22270.0116
20	4,5	3,0	6,1	22270.0020	22270.0120
22	5,5	3,5	8,1	22270.0022	22270.0122
25	5,5	3,5	11,0	22270.0025	22270.0125
28	5,5	3,5	14,0	22270.0028	22270.0128
32	6,6	4,0	22,0	22270.0032	22270.0132
36	6,6	4,0	28,0	22270.0036	22270.0136
40	6,6	5,0	44,0	22270.0040	22270.0140
45	6,6	6,0	68,0	22270.0045	22270.0145
52	6,6	6,0	92,0	22270.0052	22270.0152

적용 예

