



제품 설명


재질

- 몸체**
- 스틸, 흑색처리

연결부품

- 열처리 스틸
- 풀-로드**
- 특수 스틸

그림



주문 정보

a	b	c	g	치수					[g]	부품번호.
				h ₁	h ₂	i	k	l		
50	25	92	M12	35 - 53	25	39,5	28	40	550	23700.0212
60	30	112	M16	42 - 68	30	48,0	34	50	1140	23700.0216

적용 예

