

## 旧仕様

形番	止めねじ ds	ねじ位置 S <sub>2</sub> [mm]	六角棒スパナの 呼び	締め付けトルク (N・m)	保持器 材質	封入 グリース
MUC201	M6X1	4.5	3	3.9	ナイロン	アルバニヤゲリース S3
MUC202		4.5				
MUC203		4.5				
MUC204		4.5				
MUC205		5				
MUC206		5				
MUC207	M8X1	6	4	8.3		
MUC208		8				
MUC209		8				
MUC210	M10X1.25	9	5	16.2		
MUC211		9				
MUC212		10				
MUC213		10				