

HSBOX Plastic Enclosure

N Series



Size table

Model	Width	Height	Depth
N Series	80	110	70
	80	150	70
	80	200	70
	80	250	70
	110	110	75
	125	125	75
	130	180	100
	150	200	100
	150	200	130
	150	250	100
	150	250	130
	200	200	100
200	200	130	

Customer can choose screw type cover or hinge & latch type cover.

Covers are transparent or light gray.

IP66 certified (TUV). UL50 Type 2 listed.

Galva. steel mounting plate.

HSBOX Plastic Enclosure

Q Series



Size table

Model	Width	Height	Depth
Q Series	190	190	130
	190	280	130
	190	280	180
	190	380	130
	190	380	180
	280	280	130
	280	380	130
	280	380	180
	280	560	130
	380	560	180

Customer can choose screw type cover or hinge & latch type cover.

Covers are transparent or light gray.

IP66 certified (TUV).

Galva. steel mounting plate.