

ASL-E

●アルミスペーサー (六角) ●Low-Pb aluminum spacer (Hexagonal) ●铝隔离柱 (六角)

仕様

- ・材質/鉛レス快削アルミ (CB156) **鉛含有量10ppm以下**
- ・処理/酸洗
- ・RoHS対応製品



ASL-300E (M=3 ピッチ0.5)				L	品番	ℓ ₁	L	品番	ℓ ₁	L	品番	ℓ ₁
	4	ASL-304E	全ネジ	14	ASL-314E	全ネジ	29	ASL-329E	6			
	4.5	ASL-304.5E	//	15	ASL-315E	全ネジ	30	ASL-330E	6			
	5	ASL-305E	//	16	ASL-316E	6	35	ASL-335E	6			
	5.5	ASL-305.5E	//	16.5	ASL-316.5E	6	40	ASL-340E	6			
	6	ASL-306E	//	17	ASL-317E	6	45	ASL-345E	6			
	6.5	ASL-306.5E	//	17.5	ASL-317.5E	6	50	ASL-350E	6			
	7	ASL-307E	//	18	ASL-318E	6	55	ASL-355E	6			
	7.5	ASL-307.5E	//	19	ASL-319E	6	60	ASL-360E	6			
	8	ASL-308E	//	20	ASL-320E	6	65	ASL-365E	6			
	8.5	ASL-308.5E	//	21	ASL-321E	6	70	ASL-370E	6			
	9	ASL-309E	//	22	ASL-322E	6	75	ASL-375E	6			
	9.5	ASL-309.5E	//	23	ASL-323E	6	80	ASL-380E	6			
	10	ASL-310E	//	24	ASL-324E	6	85	ASL-385E	6			
11	ASL-311E	//	25	ASL-325E	6	90	ASL-390E	6				
12	ASL-312E	//	26	ASL-326E	6	95	ASL-395E	6				
12.5	ASL-312.5E	//	27	ASL-327E	6	100	ASL-3100E	6				
13	ASL-313E	全ネジ	28	ASL-328E	6							

Lの公差 L=60迄±0.1 L=65より±0.2
端面に鉛レス認識ミゾ付

ご注文個数 50個～

ASL-400E (M=4 ピッチ0.7)				L	品番	ℓ ₁	L	品番	ℓ ₁	L	品番	ℓ ₁
	5	ASL-405E	全ネジ	20	ASL-420E	8	55	ASL-455E	8			
	6	ASL-406E	//	21	ASL-421E	8	60	ASL-460E	8			
	7	ASL-407E	//	22	ASL-422E	8	65	ASL-465E	8			
	8	ASL-408E	//	23	ASL-423E	8	70	ASL-470E	8			
	9	ASL-409E	//	24	ASL-424E	8	75	ASL-475E	8			
	10	ASL-410E	//	25	ASL-425E	8	80	ASL-480E	8			
	11	ASL-411E	//	26	ASL-426E	8	85	ASL-485E	8			
	12	ASL-412E	//	27	ASL-427E	8	90	ASL-490E	8			
	13	ASL-413E	//	28	ASL-428E	8	95	ASL-495E	8			
	14	ASL-414E	//	29	ASL-429E	8	100	ASL-4100E	8			
	15	ASL-415E	//	30	ASL-430E	8	110	ASL-4110E	8			
	16	ASL-416E	全ネジ	35	ASL-435E	8	120	ASL-4120E	8			
	17	ASL-417E	8	40	ASL-440E	8	130	ASL-4130E	8			
18	ASL-418E	8	45	ASL-445E	8	140	ASL-4140E	8				
19	ASL-419E	8	50	ASL-450E	8	150	ASL-4150E	8				

Lの公差 L=60迄±0.1 L=65~100迄±0.2
L=110より±0.3
端面に鉛レス認識ミゾ付

ご注文個数 50個～