



PAIRCOIL 20M

Item No.	Copper tube (O.D. × Length)	Copper thickness (mm)	Insulation thickness (mm)	Pcs/Pkg
PC-2320-JE	1/4×3/8×20m	0.8×0.8	8× 8	1
PC-2420-JE	1/4×1/2×20m	0.8×0.8	8×10	1
PC-2520-JE	1/4×5/8×20m	0.8×1.0	8×10	1
PC-3520-JE	3/8×5/8×20m	0.8×1.0	8×10	1
PC-3620Z-JE	3/8×3/4×20m	0.8×1.2	8×10	1

NEOCOIL 20M

Item No.	Copper tube (O.D. × Length)	Copper thickness (mm)	Insulation thickness (mm)	Pcs/Pkg
NC-220-JE	1/4×20m	0.8	8	2
NC-320-JE	3/8×20m	0.8	8	2
NC-420-JE	1/2×20m	0.8	10	1
NC-520-JE	5/8×20m	1.0	10	1
NC-620Z-JE	3/4×20m	1.2	10	1

PAIRCOIL 30M

Item No.	Copper tube (O.D. × Length)	Copper thickness (mm)	Insulation thickness (mm)	Pcs/Pkg
PC-2330-JE	1/4×3/8×30m	0.8×0.8	8× 8	1
PC-2430-JE	1/4×1/2×30m	0.8×0.8	8×10	1
PC-2530-JE	1/4×5/8×30m	0.8×1.0	8×10	1

PAIRCOIL U TYPE 20M

Competitive Model

Item No.	Copper tube (O.D. × Length)	Copper thickness (mm)	Insulation thickness (mm)	Pcs/Pkg
PC-2320U-JE	1/4×3/8×20m	0.61×0.61	8× 8	1
PC-2420U-JE	1/4×1/2×20m	0.61×0.61	8×10	1
PC-2520U-JE	1/4×5/8×20m	0.61×0.81	8×10	1

NEOCOIL U TYPE 20M

Item No.	Copper tube (O.D. × Length)	Copper thickness (mm)	Insulation thickness (mm)	Pcs/Pkg
NC-520U-JE	5/8×20m	0.81	10	1
NC-620U-JE	3/4×20m	1.0	10	1

PAIRCOIL U TYPE 30M

Item No.	Copper tube (O.D. × Length)	Copper thickness (mm)	Insulation thickness (mm)	Pcs/Pkg
PC-2330U-JE	1/4×3/8×30m	0.61×0.61	8× 8	1
PC-2430U-JE	1/4×1/2×30m	0.61×0.61	8×10	1