

POLYGON BAND



● Aluminum oxide(A)

item no.	dia x width(mm)	RPM	grit													Q'ty/ box			
			24	36	40	60	80	100	120	150	180	240	320	400	600		800	1000	
PGB2025-A	20 x 25	20,000r.p.m.				●	●	●	●	●	●								10
PGB2525-A	25 x 25	16,000r.p.m.				●	●	●	●	●	●								10
PGB3030-A	30 x 30	13,000r.p.m.				●	●	●	●	●	●								10
PGB4530-A	45 x 30	9,000r.p.m.				●	●	●	●	●	●								10

● Zirconia(Z)

item no.	dia x width(mm)	RPM	grit													Q'ty/ box			
			24	36	40	60	80	100	120	150	180	240	320	400	600		800	1000	
PGB2025-Z	20 x 25	20,000r.p.m.			●	●	●												10
PGB2525-Z	25 x 25	16,000r.p.m.			●	●	●												10
PGB3030-Z	30 x 30	13,000r.p.m.			●	●	●												10
PGB4530-Z	45 x 30	9,000r.p.m.			●	●	●												10

POLYGON BAND Drum



item no.	outside dia x width x shaft dia x shaft length(mm)	RPM	Q'ty/ box
PGBD2025	20 x 25 x 6 x 35 (for 20x25)	20,000r.p.m.	5
PGBD2525	25 x 25 x 6 x 35 (for 25x25)	16,000r.p.m.	5
PGBD3030	30 x 30 x 6 x 35 (for 30x30)	13,000r.p.m.	5
PGBD4530	45 x 30 x 6 x 35 (for 45x30)	9,000r.p.m.	5

POLYGON BAND MINI



● Aluminum oxide(A)

item no.	dia x width (mm)	RPM	grit													Q'ty/ box			
			24	36	40	60	80	100	120	150	180	240	320	400	600		800	1000	
PGBM1020	10 x 20	25,000r.p.m.						●	●	●	●	●	●	●	●				10
PGBM1520	15 x 20	20,000r.p.m.				●	●	●	●	●	●	●	●	●	●				10

POLYGON BAND MINI Drum



item no.	outside dia x width x shaft dia x shaft length(mm)	RPM	Q'ty/ box
PGBDM1020	10 x 20 x 6 x 35 (for 10x20)	25,000r.p.m.	5
PGBDM1520	15 x 20 x 6 x 35 (for 15x20)	20,000r.p.m.	5