



H : See dimensional data(Last page)

Part No.		A(Tube O.D)		T	E	h(HEX)		ℓ	L	F
ANSI NPT	ISO/JIS Rc	in	mm	NPT/Rc	mm	in	mm	mm	mm	mm
DSA 1-2		1/16	1.59	1/8	1.3	9/16	14.29	20.8	24.8	8.9
DSA 1-4		1/16	1.59	1/4	1.3	3/4	19.05	27.0	31.0	8.9
DSA 2-2	DSA 2-R2	1/8	3.18	1/8	2.3	9/16	14.29	22.5	29.2	13.0
DSA 2-4	DSA 2-R4	1/8	3.18	1/4	2.3	3/4	19.05	27.0	33.7	13.0
	DSA 2-R6	1/8	3.18	3/8	2.3	7/8	22.23	29.7	36.4	13.0
DSA 2-8		1/8	3.18	1/2	2.3	1-1/16	26.99	34.0	40.7	13.0
DSA 3-2	DSA 3-R2	3/16	4.76	1/8	3.0	9/16	14.29	23.0	29.7	13.8
	DSA 3-R4	3/16	4.76	1/4	3.0	3/4	19.05	28.0	34.7	13.8
DSA 4-1		1/4	6.35	1/16	4.8	1/2	12.7	24.0	31.5	15.4
DSA 4-2	DSA 4-R2	1/4	6.35	1/8	4.8	9/16	14.29	24.0	31.5	15.4
DSA 4-4	DSA 4-R4	1/4	6.35	1/4	4.8	3/4	19.05	28.5	36.0	15.4
DSA 4-6		1/4	6.35	3/8	4.8	7/8	22.23	30.3	37.8	15.4
	DSA 4-R6	1/4	6.35	3/8	4.8	7/8	22.23	31.3	38.8	15.4
DSA 4-8	DSA 4-R8	1/4	6.35	1/2	4.8	1-1/16	26.99	35.8	43.3	15.4
DSA 4-12		1/4	6.35	3/4	4.8	1-5/16	33.34	37.8	45.3	15.4
DSA 5-2	DSA 5-R2	5/16	7.94	1/8	6.4	9/16	14.29	24.7	32.2	16.3
DSA 5-4	DSA 5-R4	5/16	7.94	1/4	6.4	3/4	19.05	29.5	37.0	16.3
	DSA 5-R6	5/16	7.94	3/8	6.4	7/8	22.23	32.1	39.6	16.3
DSA 5-8	DSA 5-R8	5/16	7.94	1/2	6.4	1-1/16	26.99	36.6	44.1	16.3
DSA 6-2	DSA 6-R2	3/8	9.53	1/8	7.1	5/8	15.88	25.4	32.9	17.0
DSA 6-4	DSA 6-R4	3/8	9.53	1/4	7.1	3/4	19.05	30.2	37.7	17.0
DSA 6-6		3/8	9.53	3/8	7.1	7/8	22.23	31.9	39.4	17.0
	DSA 6-R6	3/8	9.53	3/8	7.1	7/8	22.23	32.9	40.4	17.0
DSA 6-8	DSA 6-R8	3/8	9.53	1/2	7.1	1-1/16	26.99	36.5	44.0	17.0
	DSA 6-R12	3/8	9.53	3/4	7.1	1-5/16	33.34	40.3	47.8	17.0
DSA 6-16		3/8	9.53	1	7.1	1-5/8	41.28	47.6	55.1	17.0
DSA 8-2	DSA 8-R2	1/2	12.7	1/8	10.4	13/16	20.64	25.4	35.7	23.0
DSA 8-4	DSA 8-R4	1/2	12.7	1/4	10.4	13/16	20.64	31.9	42.2	23.0
DSA 8-6		1/2	12.7	3/8	10.4	7/8	22.23	31.9	42.2	23.0
	DSA 8-R6	1/2	12.7	3/8	10.4	7/8	22.23	32.9	43.2	23.0
DSA 8-8	DSA 8-R8	1/2	12.7	1/2	10.4	1-1/16	26.99	36.6	46.9	23.0
DSA 8-12		1/2	12.7	3/4	10.4	1-5/16	33.34	38.1	48.4	23.0
	DSA 8-R12	1/2	12.7	3/4	10.4	1-5/16	33.34	39.1	49.4	23.0
	DSA 8-R16	1/2	12.7	1	10.4	1-5/8	41.28	47.6	57.9	23.0
DSA 10-6	DSA 10-R6	5/8	15.88	3/8	12.7	15/16	23.81	32.0	42.3	24.6
DSA 10-8	DSA 10-R8	5/8	15.88	1/2	12.7	1-1/16	26.99	36.6	46.9	24.6
DSA 10-12		5/8	15.88	3/4	12.7	1-5/16	33.34	38.1	48.4	24.6
DSA 12-6	DSA 12-R4	3/4	19.05	1/4	15.8	1-1/16	26.99	31.8	42.1	24.6
		3/4	19.05	3/8	15.8	1-1/16	26.99	34.0	44.3	24.6
DSA 12-8	DSA 12-R8	3/4	19.05	1/2	15.8	1-1/16	26.99	36.6	46.9	24.6
DSA 12-12		3/4	19.05	3/4	15.8	1-5/16	33.34	38.1	48.4	24.6
	DSA 12-R12	3/4	19.05	3/4	15.8	1-5/16	33.34	40.1	50.4	24.6
DSA 12-16		3/4	19.05	1	15.8	1-5/8	41.28	47.6	57.9	24.6