



| Part No.  |                        | A (Tube O. D) |       | T                   | E    | h (HEX) |        | ℓ     | L    |      |
|-----------|------------------------|---------------|-------|---------------------|------|---------|--------|-------|------|------|
| ANSI NPT  | ISO/JIS R <sub>c</sub> | in            | mm    | NPT/ R <sub>c</sub> | mm   | in      | mm     | mm    | mm   |      |
| DHC 2-2   | DHC 2-R2               | 1/8           | 3.18  | 1/8                 | 1.8  | 9/16    | 14.29  | 14.0  | 31.0 |      |
| DHC 2-4   | DHC 2-R4               | 1/8           | 3.18  | 1/4                 | 1.8  | 3/4     | 19.05  | 14.0  | 34.0 |      |
| DHC 3-2   | DHC 3-R2               | 3/16          | 4.76  | 1/8                 | 3.2  | 9/16    | 14.29  | 14.8  | 32.1 |      |
| DHC 3-4   | DHC 3-R4               | 3/16          | 4.76  | 1/4                 | 3.2  | 3/4     | 19.05  | 14.8  | 34.8 |      |
| DHC 4-2   | DHC 4-R2               | 1/4           | 6.35  | 1/8                 | 4.6  | 9/16    | 14.29  | 16.5  | 33.5 |      |
| DHC 4-4   | DHC 4-R4               | 1/4           | 6.35  | 1/4                 | 4.6  | 3/4     | 19.05  | 16.5  | 36.5 |      |
| DHC 4-6   | DHC 4-R6               | 1/4           | 6.35  | 3/8                 | 4.6  | 7/8     | 22.23  | 16.5  | 39.5 |      |
| DHC 4-8   | DHC 4-R8               | 1/4           | 6.35  | 1/2                 | 4.6  | 1-1/16  | 26.99  | 16.5  | 45.2 |      |
| DHC 5-2   | DHC 5-R2               | 5/16          | 7.94  | 1/8                 | 6.4  | 9/16    | 14.29  | 17.2  | 34.3 |      |
| DHC 5-4   | DHC 5-R4               | 5/16          | 7.94  | 1/4                 | 6.4  | 3/4     | 19.05  | 17.2  | 37.1 |      |
| DHC 6-2   | DHC 6-R2               | 3/8           | 9.53  | 1/8                 | 7.1  | 9/16    | 14.29  | 18.0  | 35.3 |      |
| DHC 6-4   | DHC 6-R4               | 3/8           | 9.53  | 1/4                 | 7.1  | 3/4     | 19.05  | 18.0  | 38.0 |      |
| DHC 6-6   | DHC 6-R6               | 3/8           | 9.53  | 3/8                 | 7.1  | 7/8     | 22.23  | 18.0  | 41.0 |      |
| DHC 6-8   | DHC 6-R8               | 3/8           | 9.53  | 1/2                 | 7.1  | 1-1/16  | 26.99  | 18.0  | 46.5 |      |
| DHC 8-4   | DHC 8-R2               | 1/2           | 12.7  | 1/8                 | 9.9  | 9/16    | 14.29  | 23.5  | 40.5 |      |
|           | DHC 8-R4               | 1/2           | 12.7  | 1/4                 | 9.9  | 3/4     | 19.05  | 23.5  | 43.5 |      |
|           | DHC 8-6                | DHC 8-R6      | 1/2   | 12.7                | 3/8  | 9.9     | 7/8    | 22.23 | 23.5 | 47.0 |
|           | DHC 8-8                | DHC 8-R8      | 1/2   | 12.7                | 1/2  | 9.9     | 1-1/16 | 26.99 | 23.5 | 52.5 |
|           | DHC 8-R12              | DHC 8-R12     | 1/2   | 12.7                | 3/4  | 9.9     | 1-5/16 | 33.34 | 23.5 | 54.0 |
| DHC 10-6  | DHC 10-R6              | 5/8           | 15.88 | 3/8                 | 12.7 | 7/8     | 22.23  | 25.2  | 48.3 |      |
| DHC 10-8  | DHC 10-R8              | 5/8           | 15.88 | 1/2                 | 12.7 | 1-1/16  | 26.99  | 25.2  | 53.8 |      |
| DHC 10-12 | DHC 10-R12             | 5/8           | 15.88 | 3/4                 | 12.7 | 1-5/16  | 33.34  | 25.2  | 55.4 |      |
| DHC 12-8  | DHC 12-R8              | 3/4           | 19.05 | 1/2                 | 15.0 | 1-1/16  | 26.99  | 25.2  | 54.0 |      |
| DHC 12-12 | DHC 12-R12             | 3/4           | 19.05 | 3/4                 | 15.0 | 1-5/16  | 33.34  | 25.2  | 55.4 |      |
| DHC 12-16 | DHC 12-R16             | 3/4           | 19.05 | 1                   | 15.0 | 1-5/8   | 41.28  | 25.2  | 62.5 |      |
| DHC 14-12 | DHC 14-R12             | 7/8           | 22.23 | 3/4                 | 17.3 | 1-5/16  | 33.34  | 27.0  | 57.2 |      |
| DHC 16-12 | DHC 16-R8              | 1             | 25.4  | 1/2                 | 20.1 | 1-1/16  | 26.99  | 32.5  | 61.0 |      |
|           | DHC 16-R12             | 1             | 25.4  | 3/4                 | 20.1 | 1-5/16  | 33.34  | 32.5  | 62.0 |      |
|           | DHC 16-R16             | 1             | 25.4  | 1                   | 20.1 | 1-5/8   | 41.28  | 32.5  | 68.8 |      |