



<b>BI-LoK</b>	<b>MDBA</b>	<b>Plug for Metric tube</b>
---------------	-------------	---------------------------------



Part No.	A (O. D)	H	Snap ring
	mm	HEX	
MDBA 3M	3	12	E Type (JIS B280-2)
MDBA 4M	4	13	E Type (JIS B280-3)
MDBA 6M	6	14	E Type (JIS B280-5)
MDBA 8M	8	17	E Type (JIS B280-6)
MDBA 10M	10	19	E Type (JIS B280-7)
MDBA 12M	12	22	E Type (JIS B280-10)
MDBA 15M	15	27	C Type (JIS B2804-15)
MDBA 16M	16	27	E Type (US-62S)
MDBA 18M	18	30	E Type (FUS-S18)
MDBA 20M	20	30	E Type (US-75S)
MDBA 22M	22	32	E Type (US-87S)
MDBA 25M	25	41	E Type (US-100S)

<b>BI-LoK</b>	<b>MDCA</b>	<b>Cap Caps end of metric tube</b>
---------------	-------------	--



Part No.	A (O. D)	h	H	ℓ	L	F
	mm	HEX	HEX	mm	mm	mm
MDCA 3M	3	12	12	14.3	21.0	13.0
MDCA 4M	4	12	13	15.5	22.3	13.9
MDCA 6M	6	14	14	16.5	24.0	15.4
MDCA 8M	8	17	17	17.8	25.3	16.3
MDCA 10M	10	19	19	19.3	27.1	17.3
MDCA 12M	12	22	22	19.8	30.0	22.9
MDCA 15M	15	24	27	20.6	30.6	24.3
MDCA 16M	16	24	27	20.6	30.8	24.5
MDCA 18M	18	27	30	22.0	32.2	24.5
MDCA 20M	20	30	30	22.3	32.5	24.5
MDCA 22M	22	32	32	22.3	32.5	26.1
MDCA 25M	25	36	41	26.7	39.2	31.6