



BI-LoK	MDNA	Nut Metric tube
---------------	-------------	----------------------------




Part No.	A (Tube O. D)	H	L	T (Straight thread)
	mm	HEX	mm	
MDNA 2M	2	12	10.2	1/4-24 UN
MDNA 3M	3	12	11.9	5/16-20UN
MDNA 4M	4	13	11.9	3/8-20UN
MDNA 6M	6	14	12.7	7/16-20UNF
MDNA 8M	8	17	13.5	1/2-20UNF
MDNA 10M	10	19	15.1	5/8-20UN
MDNA 12M	12	22	17.5	3/4-20UNEF
MDNA 15M	15	27	17.4	7/8-20UNEF
MDNA 16M	16	27	17.4	7/8-20UNEF
MDNA 18M	18	30	17.4	1-20UNEF
MDNA 20M	20	30	17.4	1-1/16-20UN
MDNA 22M	22	32	17.4	1-1/8-20UN
MDNA 25M	25	41	20.6	1-5/16-20UN

BI-LoK	DOF	Front Ferrule Metric tube
---------------	------------	--------------------------------------



Part No.	A (mm)
DOF 2M	2
DOF 3M	3
DOF 4M	4
DOF 6M	6
DOF 8M	8
DOF 10M	10
DOF 12M	12
DOF 15M	15
DOF 16M	16
DOF 18M	18
DOF 20M	20
DOF 22M	22
DOF 25M	25

BI-LoK	DOB	Back Ferrule Metric tube
---------------	------------	-------------------------------------



Part No.	A (mm)
DOB 2M	2
DOB 3M	3
DOB 4M	4
DOB 6M	6
DOB 8M	8
DOB 10M	10
DOB 12M	12
DOB 15M	15
DOB 16M	16
DOB 18M	18
DOB 20M	20
DOB 22M	22
DOB 25M	25