


軸径 6 - 15 mm

軸径 mm	呼び番号		主要寸法 mm			組合せ軸受					
	一枚リップ	二枚リップ	d_1	D	b	TA…Z TLA…Z	YT YTL	RNA TAF	TR GTR	RNAF	NAX NBX
6	OS 6102.5	—	6	10	2.5	TLA 69Z		—		—	—
7	OS 7112.5	—	7	11	2.5	TLA 79Z		—		—	—
8	OS 8123	—	8	12	3	TLA 810Z		—		—	—
	OS 8153	—	8	15	3	TA 810Z TA 815Z TA 820Z YT 810		RNA 496 TAF 81512 TAF 81516		RNAF 81510	—
9	OS 9133	—	9	13	3	TLA 910Z TLA 912Z		—		—	—
	OS 9163	—	9	16	3	TA 912Z TA 916Z YT 912		TAF 91612 TAF 91616		—	—
10	OS 10143	—	10	14	3	TLA 1010Z TLA 1012Z TLA 1015Z		—		—	—
	OS 10173	—	10	17	3	TA 1010Z TA 1012Z TA 1015Z TA 1020Z		TAF 101712 TAF 101716		RNAF 101710	—