

HR-A,HR-B

BOLT REPLACEMENT KITS



HR-A



HR-B

Type	Body
HR-A	Steel (SCM440) Black oxide
HR-B	Steel (SCM440) Nickel-based coating

HR-A *HR42-A, HR48-A and HR64-A are not stock items.

Part Number	Weight (g)	Proper Hoist Rings
HR 6-A	8	HR 6
HR 8-A	20	HR 8
HR10-A	30	HR10
HR12-A	60	HR12 HR12L
HR16-A	120	HR16 HR16L
HR20-A	230	HR20 HR20L
HR24-A	400	HR24
HR30-A	910	HR30
HR36-A	1,520	HR36
HR42-A	2,750	HR42
HR48-A	3,270	HR48
HR64-A	7,120	HR64

HR-B All HR-Bs are non-stock items.

Part Number	Weight (g)	Proper Hoist Rings
HR 6-B	8	HRB 6
HR 8-B	20	HRB 8
HR10-B	30	HRB10
HR12-B	60	HRB12
HR16-B	120	HRB16
HR20-BS	210	HRB20S
HR20-B	230	HRB20
HR24-B	400	HRB24
HR30-BS	790	HRB30S
HR30-B	910	HRB30
HR36-B	1,520	HRB36
HR42-B	2,750	HRB42
HR48-B	3,270	HRB48
HR64-B	7,120	HRB64

Feature:

Contains a set of replacement bolt and retaining ring.
The bolt is magnetic particle inspected.