



PCS

POINTED TIP SCREWS



Body	Tip
S45CF steel Black oxide finish	SKS93 steel Black oxide finish HRC54-58

Part Number	M	L	d	L ₁	L ₂	w	Max. Load Capacity (Static) (kN)	Weight (g)
PCS 5×09	M 5×0.8	8.5	3	0.5	1.3	2.5	4.5	0.7
PCS 5×13		12.5						1.1
PCS 5×17		16.5						1.6
PCS 5×21		20.5						2.1
PCS 6×14	M 6×1	13.5	4	0.8	1.9	3	9	1.7
PCS 6×18		17.5						2.3
PCS 6×22		21.5						2.3
PCS 6×27		26.5						4
PCS 8×14	M 8×1.25	14	5.5	1	2.4	4	15	3.2
PCS 8×18		18						4.4
PCS 8×22		22						5.6
PCS 8×27		27						7.1
PCS 8×34		34	9.3					
PCS10×18	M10×1.5	18	7	1.5	2.6	5	20	6.7
PCS10×22		22						8.8
PCS10×27		27						11
PCS10×34		34						14.4
PCS10×42		42						18.4

Feature

A sharp pointed edge of the tip bites on a workpiece surface.

How To Use

