



DWG. NO. SJ015093-E

SYM.	DCN. NO.	DESCRIPTION	DATE	DRAWN	CHECKED	APP'D	APP'D
------	----------	-------------	------	-------	---------	-------	-------

TABLE-1

NO. OF CONTACTS	DIM.	A <sup>+0.5</sup>	B <sup>+0.25</sup>	C <sup>+0.3</sup>	D <sup>+0.3</sup>
2		5.5	2.5	2	1.5
3		8	5	3	2
4		10.5	7.5	4	2.5
5		13	10	5	3
6		15.5	12.5	6	3.5
7		18	15	6	6
8		20.5	17.5	6	8.5
9		23	20	6	11
10		25.5	22.5	6	13.5



HOW TO ORDER

IL-\*\*\*P-S3EN2-\*(N)  
 NEW TYPE (5-CONTACT ONLY)  
 INSULATOR COLOR (STANDARD COLOR)  
 LIGHT BROWN ISN'T SHOWN  
 THICKNESS OF APPLICABLE PC BOARD (2:1.6~2.4 THICK)  
 INSULATOR TYPE  
 CONTACT TYPE  
 CONTACT SPACING (25mm ONLY)  
 CONTACT ROW (SINGLE ONLY)  
 POST SIDE  
 NO. OF CONTACTS (SEE TABLE 1)  
 SERIES PREFIX

NOTE 1. NO PLATING ON THESE AREAS.

APPLICATION	USED ON	NEXT ASS'Y	FINAL ASS'Y

UNLESS OTHERWISE SPECIFIED		DATE	DEC. 1977
DIMENSIONS ARE IN MILLIMETERS		DRAWN	E. MURANO
TOLERANCES ON:		CHECKED	H. Takada
FRACTIONS	DECIMALS	ANGLES	APP'D T. SOMEI
	±0.08	±0.5	±0.2
TREATMENT OR FINISH		APP'D	Joe Sando

2	INSULATOR	1	THERMOPLASTIC		
1	CONTACT	SEE REF	COPPER ALLOY	TIN OVER NICKEL	
ITEM	DESCRIPTION	Q'TY	MATERIAL	FINISH	PART NO.
<p>TITLE: STRIGHT PIN HEADER Reference Only</p> <p>IL-***P-S3EN2-*</p>					
<p>JAE-CONNECTOR.COM</p> <p>IND. CO., LTD. FACTORY</p> <p>NAKACAMI-CHO, AKISHIMA-SHI, TOKYO, JAPAN</p>					
<p>DWG. NO. SJ015093-E</p> <p>SHEET 1 OF 1</p>					

3rd Angle Drawing

SCALE x 4 DWG. SIZE B WT.