

一般・給水・給湯配管用継手品種と寸法表

■PL継手(樹脂コーティング品) JIS規格品

品種 略号 呼び(B)	エルボ	45°エルボ	ストリート エルボ	チー	クロス	キャップ	ソケット	フランジ	プラグ	ユニオン	ニップル
	L	45°L	SL	T	CR	CA	S	F	P	U	NI
1/2	●	●	●	●	●	●	●	●	●	●	●
3/4	●	●	●	●	●	●	●	●	●	●	●
1	●	●	●	●	●	●	●	●	●	●	●
1 1/4	●	●	●	●	●	●	●	●	●	●	●
1 1/2	●	●	●	●	●	●	●	●	●	●	●
2	●	●	●	●	●	●	●	●	●	●	●
2 1/2	●	●	●	●	●	●	●	●	●	●	●
3	●	●	●	●	●	●	●	●	●	●	●
4	●	●	●	●	●	●	●	●	●	●	●
5	●	●	●	●	●	●	●	●	●	●	●
6	●	●	●	●	●	●	●	●	●	●	●

■一部の商品は、JIS規格品ではありませんが、JIS規格に準拠しております。(詳しくは当社管継手カタログをご参照下さい。)

品種 略号 呼び(B)	径違い エルボ	径違い チー	径違い ソケット	プッシング
	RL	RT	RS	BU
3/4 × 1/2	●	●	●	●
1 × 1/2	●	●	●	●
1 × 3/4	●	●	●	●
1 1/4 × 1/2	●	●	●	●
1 1/4 × 3/4	●	●	●	●
1 1/4 × 1	●	●	●	●
1 1/2 × 1/2	●	●	●	●
1 1/2 × 3/4	●	●	●	●
1 1/2 × 1	●	●	●	●
1 1/2 × 1 1/4	●	●	●	●
2 × 1/2	●	●	●	●
2 × 3/4	●	●	●	●
2 × 1	●	●	●	●
2 × 1 1/4	●	●	●	●
2 × 1 1/2	●	●	●	●
2 1/2 × 1/2	●	●	●	●
2 1/2 × 3/4	●	●	●	●

品種 略号 呼び(B)	径違い エルボ	径違い チー	径違い ソケット	プッシング
	RL	RT	RS	BU
2 1/2 × 1	●	●	●	●
2 1/2 × 1 1/4	●	●	●	●
2 1/2 × 1 1/2	●	●	●	●
2 1/2 × 2	●	●	●	●
3 × 1/2	●	●	●	●
3 × 3/4	●	●	●	●
3 × 1	●	●	●	●
3 × 1 1/4	●	●	●	●
3 × 1 1/2	●	●	●	●
3 × 2	●	●	●	●
3 × 2 1/2	●	●	●	●
4 × 1/2	●	●	●	●
4 × 3/4	●	●	●	●
4 × 1	●	●	●	●
4 × 1 1/4	●	●	●	●
4 × 1 1/2	●	●	●	●
4 × 2	●	●	●	●

品種 略号 呼び(B)	径違い エルボ	径違い チー	径違い ソケット	プッシング
	RL	RT	RS	BU
4 × 2 1/2	●	●	●	●
4 × 3	●	●	●	●
5 × 1	●	●	●	●
5 × 1 1/4	●	●	●	●
5 × 1 1/2	●	●	●	●
5 × 2	●	●	●	●
5 × 2 1/2	●	●	●	●
5 × 3	●	●	●	●
5 × 4	●	●	●	●
6 × 1	●	●	●	●
6 × 1 1/4	●	●	●	●
6 × 1 1/2	●	●	●	●
6 × 2	●	●	●	●
6 × 2 1/2	●	●	●	●
6 × 3	●	●	●	●
6 × 4	●	●	●	●
6 × 5	●	●	●	●

■一部の商品は、JIS規格品ではありませんが、JIS規格に準拠しております。(詳しくは当社管継手カタログをご参照下さい。)

■PLパイプニップル(樹脂コーティング品)

(パレルニップル)

呼び(B)	長さmm	
1/2	34	●
3/4	38	●
1	42	●
1 1/4	50	●
1 1/2	50	●
2	58	●
2 1/2	70	●
3	78	●
4	90	●
5	103	●
6	103	●

(ロングニップル)

呼び(B) 長さmm	1/2	3/4	1	1 1/4	1 1/2	2	2 1/2	3	4	5	6
	50mm	●	●	●							
65mm	●	●	●	●	●	●					
75mm	●	●	●	●	●	●	●				
90mm	●	●	●	●	●	●	●	●			
100mm	●	●	●	●	●	●	●	●	●		
115mm	●	●	●	●	●	●	●	●	●	●	
125mm	●	●	●	●	●	●	●	●	●	●	●
140mm	●	●	●	●	●	●	●	●	●	●	●
150mm	●	●	●	●	●	●	●	●	●	●	●
175mm	●	●	●	●	●	●	●	●	●	●	●
200mm	●	●	●	●	●	●	●	●	●	●	●
250mm	●	●	●	●	●	●	●	●	●	●	●
300mm	●	●	●	●	●	●	●	●	●	●	●