

架空用

品種と寸法



品種 略号 呼び (B)	エルボ	チー	ソケット	45°エルボ	フランジ	ニップル	プッシング	SCH40 パイプニップル
	HBL・ HBRL	HBT・ HBRT	HBS・ HBRS	45HBL	HF	HNI	HBU	SCH40 P-NI
3/4	●		●					
1	●		●					
1 1/2	●		●					
2	●		●		●			※●
2 1/2	●	●	●	●	●	●		※●
3	●	●	●	●	●	●		
4	●	●	●	●	●	●		※●
5	●	●	●	●	●			※●
2 × 1 1/2			●					
2 1/2 × 1 1/2							●	
2 1/2 × 2							●	
3 × 3/4							●	
3 × 1		●						
3 × 2 1/2	●	●	●					
4 × 3/4							●	
4 × 1		●					●	
4 × 2		●	●				●	
4 × 2 1/2	●	●	●					
4 × 3	●	●					●	
5 × 2 1/2		●						
5 × 4			●					

※パイプニップルは(財)日本消防設備安全センター認定品外です。

エルボ

呼び	A
3/4	36.5
1	41.5
1 1/2	54.0
2	63.5
2 1/2	74.5
3	86.0
4	105.0
5	125.0

単位: mm

呼び	A
3/4	36.5
1	41.5
1 1/2	54.0
2	63.5
2 1/2	74.5
3	86.0
4	105.0
5	125.0

径違いエルボ

呼び ①×②	A	B
3 × 2 1/2	77.5	84.0
4 × 2 1/2	82.5	100.0
4 × 3	89.0	102.0

単位: mm

呼び ①×②	A	B
3 × 2 1/2	77.5	84.0
4 × 2 1/2	82.5	100.0
4 × 3	89.0	102.0

チー

呼び	A
2 1/2	74.5
3	86.0
4	105.0
5	125.0

単位: mm

呼び	A
2 1/2	74.5
3	86.0
4	105.0
5	125.0

径違いチー

呼び ①×②	A	B
3 × 1	58.7	73.0
3 × 2 1/2	77.5	84.0
4 × 1	61.5	93.0
4 × 2	73.5	97.0
4 × 2 1/2	82.5	100.0
4 × 3	89.0	102.0
5 × 2 1/2	88.5	115.0

単位: mm

呼び ①×②	A	B
3 × 1	58.7	73.0
3 × 2 1/2	77.5	84.0
4 × 1	61.5	93.0
4 × 2	73.5	97.0
4 × 2 1/2	82.5	100.0
4 × 3	89.0	102.0
5 × 2 1/2	88.5	115.0

ソケット

呼び	L	呼び	L
3/4	54.0	4	112.0
1	60.5	5	125.0
1 1/2	73.0	2 × 1 1/2	81.0
2	92.0	3 × 2 1/2	103.0
2 1/2	105.0	4 × 2	110.0
3	105.0	4 × 2 1/2	110.0
		5 × 4	125.0

単位: mm

呼び	L	呼び	L
3/4	54.0	4	112.0
1	60.5	5	125.0
1 1/2	73.0	2 × 1 1/2	81.0
2	92.0	3 × 2 1/2	103.0
2 1/2	105.0	4 × 2	110.0
3	105.0	4 × 2 1/2	110.0
		5 × 4	125.0

45°エルボ

呼び	A45°
2 1/2	57.0
3	63.5
4	74.5
5	84.0

単位: mm

呼び	A45°
2 1/2	57.0
3	63.5
4	74.5
5	84.0