




外面一層ポリエチレン被覆水道用ポリエチレン粉体ライニング鋼管用 兼用形管端防食継手
水道用内外面硬質塩化ビニルライニング鋼管用



■ 接続構造図



呼び (B)	品種 略号 品名	径違いエルボ		径違いチー		径違いソケット	
		RL		RT		RS	
		Cコア	CDコア	Cコア	CDコア	Cコア	CDコア
3/4 × 1/2		●	●	●	●	●	●
1 × 1/2		●		●	●	●	●
1 × 3/4		●	●	●	●	●	●
1 1/4 × 3/4		●		●	●	●	●
1 1/4 × 1		●	●	●	●	●	●
1 1/2 × 1/2						●	
1 1/2 × 3/4		●		●	●	●	
1 1/2 × 1		●		●	●	●	●
1 1/2 × 1 1/4		●		●	●	●	●
2 × 3/4		●		●	●	●	
2 × 1		●	●	●	●	●	●
2 × 1 1/4		●		●	●	●	●
2 × 1 1/2		●	●	●	●	●	●
2 1/2 × 3/4				●			
2 1/2 × 1				●			
2 1/2 × 1 1/4				●			
2 1/2 × 1 1/2		●		●		●	

呼び (B)	品種 略号 品名	径違いエルボ		径違いチー		径違いソケット	
		RL		RT		RS	
		Cコア	CDコア	Cコア	CDコア	Cコア	CDコア
2 1/2 × 2		●	●	●	●	●	●
3 × 3/4				●			
3 × 1				●			
3 × 1 1/4				●			
3 × 1 1/2				●		●	
3 × 2		●		●	●	●	●
3 × 2 1/2		●	●	●	●	●	●
4 × 3/4				●			
4 × 1				●			
4 × 1 1/4				●			
4 × 1 1/2				●			
4 × 2		●		●	●	●	●
4 × 2 1/2		●		●	●	●	●
4 × 3		●	●	●	●	●	●
5 × 4				●		●	
6 × 4				●			
6 × 5						●	

CDコア 施工の際、併せてご使用下さい。



水道用内外面硬質塩化ビニルライニング鋼管製
VDパイプニップル
〔略号：VD-PNI〕



外面一層ポリエチレン被覆
水道用ポリエチレン粉体ライニング鋼管製
PDパイプニップル
〔略号：PD-PNI〕

単位:mm

品種 (略号)	ロングニップル(全長)				
	VD-PNI・PD-PNI				
	75	100	125	150	200
1/2	●	●	●	●	
3/4	●	●	●	●	
1	●	●	●	●	
1 1/4				●	
1 1/2				●	
2				●	
2 1/2					●
3					●
4					●

※ライニング鋼管製パイプニップルは日水協認証登録外品です。