

HAND OPERATED INSTALLATION TOOLS



JOT 2065-3

- For cable tie thickness up to 0.3mm width up to 7.9mm steel plate (Tpr trigger handle)
- Automatically tensions and cuts off tie when predetermined tension is reached

Strength Level	Tension strength Minimun
1	31.5kgs
2	47kgs
3	58.7kgs
4	65kgs



JOT 2065-2

- For cable tie thickness up to 0.3mm width up to 7.9mm steel plate
- Tool tension is controlled by installer - lever action cut-off



JOT-285

- For cable tie thickness up to 0.38mm width up to 10mm steel plate
- Tool tension is controlled by installer - lever action cut-off



JOT-240

- For cable tie thickness up to 1.2mm width up to 19mm steel plate
- Durable tensioner with cutter and hammer knob for binding irregular



JOT-210

- For cable tie thickness up to 1.2mm width up to 19mm steel plate
- Push bar tensioner with breaker nose to cut the strap



D