

輕少荷重
경소하중
MINIMAL LOAD

CF

하중 荷重 ±10%
직각도 直角度 2° 以下
자유장 自由長 50m/m 以下 ±0.5m/m
55m/m 以上 ± 1%

呼稱 호 칭 Model	外徑 외경(mm) Outer Dia.	內徑 내경(mm) Inner Dia.	自由長 자유장(mm) Free length	定數 정수(kgf/mm) spring constant	30万 (0.3million)		50万 (0.5 million)		100万 (1 million)	
					變形量 변형량(mm) Deflection	荷重 하중(kgf) Load	變形量 변형량(mm) Deflection	荷重 하중(kgf) Load	變形量 변형량(mm) Deflection	荷重 하중(kgf) Load
CF 60×60	60	33	60	9.59	288	30.0	259	27.0	230	24.0
70			70	8.22		35.0		31.5		28.0
80			80	7.19		40.0		36.0		32.0
90			90	6.40		45.0		40.5		36.0
100			100	5.76		50.0		45.0		40.0
125			125	4.60		62.5		56.2		50.0
150			150	3.84		75.0		67.5		60.0
175			175	3.29		87.5		78.7		70.0
200			200	2.88		100.0		90.0		80.0
225			225	2.56		112.5		101.3		90.0
250			250	2.30		125.0		112.5		100.0
275			275	2.09		137.5		123.8		110.0
300			300	1.92		150.0		135.0		120.0
350			350	1.65		175.0		157.5		140.0
400			400	1.44		200.0		180.0		160.0
450			450	1.28		225.0		202.5		180.0
500			500	1.15		250.0		225.0		200.0
CF 70×70	70	38.5	70	11.43	400	35.0	360	31.5	320	28.0
80			80	10.00		40.0		36.0		32.0
90			90	8.89		45.0		40.5		36.0
100			100	8.00		50.0		45.0		40.0
125			125	6.40		62.5		56.2		50.0
150			150	5.33		75.0		67.5		60.0
175			175	4.57		87.5		78.7		70.0
200			200	4.00		100.0		90.0		80.0
225			225	3.56		112.5		101.3		90.0
250			250	3.20		125.0		112.5		100.0
275			275	2.91		137.5		123.8		110.0
300			300	2.67		150.0		135.0		120.0
350			350	2.29		175.0		157.5		140.0