

輕荷重
경하중
LIGHT LOAD



하중 荷重 ±10%
직각도 直角度 2° 以下
자유장 自由長 50m/m 以下 ±0.5m/m
55m/m 以上 ± 1%

呼稱 호 칭 Model	外徑 외경(mm) Outer Dia.	內徑 내경(mm) Inner Dia.	自由長 자유장(mm) Free length	定數 정수(kgf/mm) spring constant	30万 (0.3million)		50万 (0.5 million)		100万 (1 million)	
					變形量 변형량(mm) Deflection	荷重 하중(kgf) Load	變形量 변형량(mm) Deflection	荷重 하중(kgf) Load	變形量 변형량(mm) Deflection	荷重 하중(kgf) Load
CL 18×20	18	9	20	5.42	8.0	43	7.2	39	6.4	34
25			25	4.30	10.0		9.0		8.0	
30			30	3.58	12.0		10.8		9.6	
35			35	3.07	14.0		12.6		11.2	
40			40	2.69	16.0		14.4		12.8	
45			45	2.39	18.0		16.2		14.4	
50			50	2.15	20.0		18.0		16.0	
55			55	1.96	22.0		19.8		17.6	
60			60	1.79	24.0		21.6		19.2	
65			65	1.66	26.0		23.4		20.8	
70			70	1.54	28.0		25.2		22.4	
75			75	1.44	30.0		27.0		24.0	
80			80	1.35	32.0		28.8		25.6	
90			90	1.20	36.0		32.4		28.8	
100			100	1.07	40.0		36.0		32.0	
125	125	0.86	50.0	45.0	40.0					
CL 20×20	20	10	20	6.81	8.0	54	7.2	48	6.4	43
25			25	5.40	10.0		9.0		8.0	
30			30	4.50	12.0		10.8		9.6	
35			35	3.86	14.0		12.6		11.2	
40			40	3.38	16.0		14.4		12.8	
45			45	3.00	18.0		16.2		14.4	
50			50	2.70	20.0		18.0		16.0	
55			55	2.45	22.0		19.8		17.6	
60			60	2.25	24.0		21.6		19.2	
65			65	2.08	26.0		23.4		20.8	
70			70	1.93	28.0		25.2		22.4	
75			75	1.80	30.0		27.0		24.0	
80			80	1.69	32.0		28.8		25.6	
90			90	1.50	36.0		32.4		28.8	
100			100	1.35	40.0		36.0		32.0	
125			125	1.08	50.0		45.0		40.0	
150			150	0.90	60.0		54.0		48.0	
175	175	0.77	70.0	63.0	56.0					
CL 22×25	22	11	25	6.70	10.0	67	9.0	60	8.0	54
30			30	5.60	12.0		10.8		9.6	
35			35	4.80	14.0		12.6		11.2	
40			40	4.20	16.0		14.4		12.8	
45			45	3.72	18.0		16.2		14.4	
50			50	3.35	20.0		18.0		16.0	
55			55	3.05	22.0		19.8		17.6	
60			60	2.80	24.0		21.6		19.2	
65			65	2.58	26.0		23.4		20.8	
70			70	2.40	28.0		25.2		22.4	
75			75	2.23	30.0		27.0		24.0	
80			80	2.10	32.0		28.8		25.6	
90			90	1.86	36.0		32.4		28.8	
100			100	1.68	40.0		36.0		32.0	
125			125	1.34	50.0		45.0		40.0	
150	150	1.12	60.0	54.0	48.0					
175	175	0.96	70.0	63.0	56.0					