

輕荷重
경하중
LIGHT LOAD



하중 荷重 ±10%
직각도 直角度 2° 以下
자유장 自由長 50m/m 以下 ±0.5m/m
55m/m 以上 ± 1%

呼稱 호 칭 Model	外徑 외경(mm) Outer Dia.	內徑 내경(mm) Inner Dia.	自由長 자유장(mm) Free length	定數 정수(kgf/mm) spring constant	30万 (0.3million)		50万 (0.5 million)		100万 (1 million)	
					變形量 변형량(mm) Deflection	荷重 하중(kgf) Load	變形量 변형량(mm) Deflection	荷重 하중(kgf) Load	變形量 변형량(mm) Deflection	荷重 하중(kgf) Load
CL 60×60	60	30	60	20.25	486	24.0	438	21.6	389	19.2
70			70	17.35		28.0		25.2		22.4
80			80	15.18		32.0		28.8		25.6
90			90	13.50		36.0		32.4		28.8
100			100	12.15		40.0		36.0		32.0
125			125	9.72		50.0		45.0		40.0
150			150	8.10		60.0		54.0		48.0
175			175	6.94		70.0		63.0		56.0
200			200	6.07		80.0		72.0		64.0
225			225	5.40		90.0		81.0		72.0
250			250	4.86		100.0		90.0		80.0
275			275	4.42		110.0		99.0		88.0
300			300	4.05		120.0		108.0		96.0
350			350	3.47		140.0		126.0		112.0
400			400	3.04		160.0		144.0		128.0
450			450	2.70		180.0		162.0		144.0
500	500	2.43	200.0	180.0	160.0					
CL 70×70	70	38.5	70	21.79	610	28.0	549	25.2	488	22.4
80			80	19.06		32.0		28.8		25.6
90			90	16.94		36.0		32.4		28.8
100			100	15.25		40.0		36.0		32.0
125			125	12.20		50.0		45.0		40.0
150			150	10.17		60.0		54.0		48.0
175			175	8.71		70.0		63.0		56.0
200			200	7.62		80.0		72.0		64.0
225			225	6.78		90.0		81.0		72.0
250			250	6.10		100.0		90.0		80.0
275			275	5.55		110.0		99.0		88.0
300			300	5.08		120.0		108.0		96.0
350	350	4.36	140.0	126.0	112.0					