

中荷重  
중하중  
MEDIUM LOAD



하중 荷重 ±10%  
직각도 直角度 2° 以下  
자유장 自由長 50m/m 以下 ±0.5m/m  
55m/m 以上 ± 1%

呼稱 호 칭 Model	外徑 외경(mm) Outer Dia.	內徑 내경(mm) Inner Dia.	自由長 자유장(mm) Free length	定數 정수(kgf/mm) spring constant	30万 (0.3million)		50万 (0.5 million)		100万 (1 million)	
					變形量 변형량(mm) Deflection	荷重 하중(kgf) Load	變形量 변형량(mm) Deflection	荷重 하중(kgf) Load	變形量 변형량(mm) Deflection	荷重 하중(kgf) Load
CM 18×20	18	9	20	10.00	6.4	65	5.8	59	5.1	52
25			25	8.12	8.0		7.2		6.4	
30			30	6.77	9.6		8.6		7.7	
35			35	5.80	11.2		10.1		9.0	
40			40	5.07	12.8		11.5		10.2	
45			45	4.51	14.4		13.0		11.5	
50			50	4.06	16.0		14.4		12.8	
55			55	3.69	17.6		15.8		14.1	
60			60	3.38	19.2		17.3		15.4	
65			65	3.12	20.8		18.7		16.6	
70			70	2.90	22.4		20.2		17.9	
75			75	2.70	24.0		21.6		19.2	
80			80	2.53	25.6		23.0		20.5	
90			90	2.25	28.8		25.9		23.0	
100			100	2.02	32.0		28.8		25.6	
125	125	1.62	40.0	36.0	32.0					
CM 20×20	20	10	20	12.41	6.4	80	5.8	72	5.1	64
25			25	10.00	8.0		7.2		6.4	
30			30	8.33	9.6		8.6		7.7	
35			35	7.14	11.2		10.1		9.0	
40			40	6.25	12.8		11.5		10.2	
45			45	5.55	14.4		13.0		11.5	
50			50	5.00	16.0		14.4		12.8	
55			55	4.54	17.6		15.8		14.1	
60			60	4.16	19.2		17.3		15.4	
65			65	3.84	20.8		18.7		16.6	
70			70	3.57	22.4		20.2		17.9	
75			75	3.33	24.0		21.6		19.2	
80			80	3.12	25.6		23.0		20.5	
90			90	2.77	28.8		25.9		23.0	
100			100	2.50	32.0		28.8		25.6	
125	125	2.00	40.0	36.0	32.0					
150	150	1.67	48.0	43.2	38.4					
175	175	1.43	56.0	50.4	44.8					
CM 22×25	22	11	25	12.13	8.0	97	7.2	87	6.4	78
30			30	10.10	9.6		8.6		7.7	
35			35	8.65	11.2		10.1		9.0	
40			40	7.57	12.8		11.5		10.2	
45			45	6.74	14.4		13.0		11.5	
50			50	6.06	16.0		14.4		12.8	
55			55	5.50	17.6		15.8		14.1	
60			60	5.05	19.2		17.3		15.4	
65			65	4.66	20.8		18.7		16.6	
70			70	4.33	22.4		20.2		17.9	
75			75	4.04	24.0		21.6		19.2	
80			80	3.78	25.6		23.0		20.5	
90			90	3.36	28.8		25.9		23.0	
100			100	3.03	32.0		28.8		25.6	
125			125	2.42	40.0		36.0		32.0	
150	150	2.01	48.0	43.2	38.4					
175	175	1.73	56.0	50.4	44.8					