

重荷重
중하중
HEAVY LOAD

CH

하중 荷重 ±10%
직각도 直角度 2° 以下
자유장 自由長 50m/m 以下 ±0.5m/m
55m/m 以上 ± 1%

呼稱 호칭 Model	外徑 외경(mm) Outer Dia.	內徑 내경(mm) Inner Dia.	自由長 자유장(mm) Free length	定數 정수(kgf/mm) spring constant	30万 (0.3million)		50万 (0.5 million)		100万 (1 million)	
					變形量 변형량(mm) Deflection	荷重 하중(kgf) Load	變形量 변형량(mm) Deflection	荷重 하중(kgf) Load	變形量 변형량(mm) Deflection	荷重 하중(kgf) Load
CH 60×60	60	30	60	75.00	14.4	1080	13.0	973	11.5	864
70			70	64.28	16.8		15.1		13.4	
80			80	56.25	19.2		17.3		15.4	
90			90	50.00	21.6		19.4		17.3	
100			100	45.00	24.0		21.6		19.2	
125			125	36.00	30.0		27.0		24.0	
150			150	30.00	36.0		32.4		28.8	
175			175	25.71	42.0		37.8		33.6	
200			200	22.50	48.0		43.2		38.4	
225			225	20.00	54.0		48.6		43.2	
250			250	18.00	60.0		54.0		48.0	
275			275	16.36	66.0		59.4		52.8	
300			300	15.00	72.0		64.8		57.6	
350			350	12.86	84.0		75.6		67.2	
CH 70×70	70	38.5	70	76.2	16.8	1280	15.1	1152	13.4	1024
80			80	66.7	19.2		17.3		15.4	
90			90	59.3	21.6		19.4		17.3	
100			100	53.3	24.0		21.6		19.2	
125			125	42.7	30.0		27.0		24.0	
150			150	35.6	36.0		32.4		28.8	
175			175	30.5	42.0		37.8		33.6	
200			200	26.7	48.0		43.2		38.4	
225			225	23.7	54.0		48.6		43.2	
250			250	21.3	60.0		54.0		48.0	
275			275	19.4	66.0		59.4		52.8	
300			300	17.8	72.0		64.8		57.6	
350			350	15.2	84.0		75.6		67.2	