

極重荷重
극중하중
EXTRA HEAVY LOAD

CB

하중 荷重 ±10%
직각도 直角度 2° 以下
자유장 自由長 50m/m 以下 ±0.5m/m
55m/m 以上 ± 1%

呼稱 호 칭 Model	外徑 외경(mm) Outer Dia.	內徑 내경(mm) Inner Dia.	自由長 자유장(mm) Free length	定數 정수(kgf/mm) spring constant	30万 (0.3million)		50万 (0.5 million)		100万 (1 million)	
					變形量 변형량(mm) Deflection	荷重 하중(kgf) Load	變形量 변형량(mm) Deflection	荷重 하중(kgf) Load	變形量 변형량(mm) Deflection	荷重 하중(kgf) Load
CB 25×25	25	12.5	25	49.00	5.0	245	4.5	220	4.0	196
30			30	40.80	6.0		5.4		4.8	
35			35	35.00	7.0		6.3		5.6	
40			40	30.60	8.0		7.2		6.4	
45			45	27.20	9.0		8.1		7.2	
50			50	24.50	10.0		9.0		8.0	
55			55	22.30	11.0		9.9		8.8	
60			60	20.40	12.0		10.8		9.6	
65			65	18.80	13.0		11.7		10.4	
70			70	17.50	14.0		12.6		11.2	
75			75	16.30	15.0		13.5		12.0	
80			80	15.30	16.0		14.4		12.8	
90			90	13.60	18.0		16.2		14.4	
100			100	12.30	20.0		18.0		16.0	
125			125	9.80	25.0		22.5		20.0	
150			150	8.17	30.0		27.0		24.0	
175			175	7.00	35.0		31.5		28.0	
200	200	6.13	40.0	36.0	32.0					
CB 27×25	27	13.5	25	58.00	5.0	290	4.5	261	4.0	232
30			30	48.33	6.0		5.4		4.8	
35			35	41.43	7.0		6.3		5.6	
40			40	36.25	8.0		7.2		6.4	
45			45	32.22	9.0		8.1		7.2	
50			50	29.00	10.0		9.0		8.0	
55			55	26.36	11.0		9.9		8.8	
60			60	24.17	12.0		10.8		9.6	
65			65	22.31	13.0		11.7		10.4	
70			70	20.71	14.0		12.6		11.2	
75			75	19.33	15.0		13.5		12.0	
80			80	18.13	16.0		14.4		12.8	
90			90	16.11	18.0		16.2		14.4	
100			100	14.50	20.0		18.0		16.0	
125			125	11.60	25.0		22.5		20.0	
150			150	9.67	30.0		27.0		24.0	
175			175	8.28	35.0		31.5		28.0	
200	200	7.25	40.0	36.0	32.0					
CB 30×25	30	15	25	72.00	5.0	360	4.5	324	4.0	288
30			30	60.00	6.0		5.4		4.8	
35			35	51.43	7.0		6.3		5.6	
40			40	45.00	8.0		7.2		6.4	
45			45	40.00	9.0		8.1		7.2	
50			50	36.00	10.0		9.0		8.0	
55			55	32.72	11.0		9.9		8.8	
60			60	30.00	12.0		10.8		9.6	
65			65	27.69	13.0		11.7		10.4	
70			70	25.71	14.0		12.6		11.2	
75			75	24.00	15.0		13.5		12.0	
80			80	22.50	16.0		14.4		12.8	
90			90	20.00	18.0		16.2		14.4	
100			100	18.00	20.0		18.0		16.0	
125			125	14.40	25.0		22.5		20.0	
150			150	12.00	30.0		27.0		24.0	
175			175	10.28	35.0		31.5		28.0	
200	200	9.00	40.0	36.0	32.0					