

極重荷重
극중하중
EXTRA HEAVY LOAD

CB

하중 荷重 ±10%
직각도 直角度 2° 以下
자유장 自由長 50m/m 以下 ±0.5m/m
55m/m 以上 ± 1%

| 呼稱 호 칭 Model | 外徑 외경(mm) Outer Dia. | 內徑 내경(mm) Inner Dia. | 自由長 자유장(mm) Free length | 定數 정수(kgf/mm) spring constant | 30万 (0.3million) | | 50万 (0.5,million) | | 100万 (1 million) | |
|--------------------|-------------------------------|-------------------------------|-------------------------------|--|------------------------------|-----------------------|------------------------------|-----------------------|------------------------------|-----------------------|
| | | | | | 變形量 변형량(mm) Deflection | 荷重 하중(kgf) Load | 變形量 변형량(mm) Deflection | 荷重 하중(kgf) Load | 變形量 변형량(mm) Deflection | 荷重 하중(kgf) Load |
| CB 60×60 | 60 | 30 | 60 | 120.00 | 12.0 | 1440 | 10.8 | 1296 | 9.6 | 1152 |
| 70 | | | 70 | 102.86 | 14.0 | | 12.6 | | 11.2 | |
| 80 | | | 80 | 90.00 | 16.0 | | 14.4 | | 12.8 | |
| 90 | | | 90 | 80.00 | 18.0 | | 16.2 | | 14.4 | |
| 100 | | | 100 | 72.00 | 20.0 | | 18.0 | | 16.0 | |
| 125 | | | 125 | 57.60 | 25.0 | | 22.5 | | 20.0 | |
| 150 | | | 150 | 48.00 | 30.0 | | 27.0 | | 24.0 | |
| 175 | | | 175 | 41.14 | 35.0 | | 31.5 | | 28.0 | |
| 200 | | | 200 | 36.00 | 40.0 | | 36.0 | | 32.0 | |
| 225 | | | 225 | 32.00 | 45.0 | | 40.5 | | 36.0 | |
| 250 | | | 250 | 28.80 | 50.0 | | 45.0 | | 40.0 | |
| 275 | | | 275 | 26.18 | 55.0 | | 49.5 | | 44.0 | |
| 300 | | | 300 | 24.00 | 60.0 | | 54.0 | | 48.0 | |
| 350 | | | 350 | 20.57 | 70.0 | | 63.0 | | 56.0 | |