

ステンレス鋼
Bシリーズ
5K/10K

ゲート(SCS13A)
10K



JV

ゲート(SCS14A)
10K





JV

グローブ(SCS13A)
5K



グローブ(SCS13A)
10K



製品記号	UEB			UEBM			UAB			UCL			
	呼び径	L	H	D	L	H	D	L	H	D	L	H	D
1/4 ^B	8 ^A										44.0	68.0	55.0
3/8	10							73.0	106.0	70.0	48.0	68.0	55.0
1/2	15	85.0	99.0	70.0				85.0	106.0	70.0	52.0	68.0	55.0
3/4	20	95.0	105.0	70.0				95.0	108.0	70.0	60.0	93.0	60.0
1	25	100.0	116.0	80.0	100.0	116.0	80.0	108.0	119.0	80.0	72.0	100.0	70.0
1 1/4	32	110.0	128.0	80.0	110.0	128.0	80.0	120.0	142.0	90.0	80.0	122.0	80.0
1 1/2	40	125.0	170.0	100.0	125.0	170.0	100.0	135.0	155.0	90.0	90.0	138.0	90.0
2	50	140.0	188.0	100.0	140.0	188.0	100.0	155.0	186.0	115.0	100.0	153.0	100.0
2 1/2	65	170.0	248.0	135.0	170.0	248.0	135.0						
3	80	190.0	275.0	155.0	190.0	275.0	155.0						
ボデー	SCS13A			SCS14A			SCS13A			SCS13A			
ボンネット	SCS13A/SUS304			SCS14A/SUS316			SCS13A			SCS13A			
ステム	SUS304			SUS316			SUS304+ハードCrめっき			SUS304+ハードCrめっき			
ジスク	SCS13A			SCS14A			SUS304			SUS304			
パッキン	膨張黒鉛+PTFE編組			膨張黒鉛+PTFE編組			膨張黒鉛+PTFE編組			PTFE:1/4 ^B -1/2 ^B 膨張黒鉛+PTFE編組:3/4 ^B -2 ^B			
ハンドル	ZDC:15 ^A -20 ^A ADC12:25 ^A -80 ^A			ADC12			ZDC:10 ^A -20 ^A ADC12:25 ^A -50 ^A			ZDC:1/4 ^B -1 ^B ADC12:1 1/4 ^B -2 ^B ねじ込み:JIS B0203			
接続形状	フランジ:JIS B2220 10K			フランジ:JIS B2220 10K			フランジ:JIS B2220 5K			ねじ込み:JIS B0203			
最高許容圧力	圧力-温度基準:SUS46			圧力-温度基準:SUS46			圧力-温度基準:SUS46			圧力-温度基準:SUS46			
備考	・JV8-1相当:15 ^A -50 ^A ・RoHS指令相当品			・JV8-1相当:25 ^A -50 ^A ・RoHS指令相当品			RoHS指令相当品			RoHS指令相当品			

ステンレス鋼
Bシリーズ
10K

グローブ(SCS13A)
10K



JV

グローブ(SCS14A)
10K



JV


グローブ(SCS13A)
10K



グローブ(SCS13A)
10K



JV



製品記号	UJ			UJM			UCB			UJB			
	呼び径	L	H	D	L	H	D	L	H	D	L	H	D
3/8 ^B	10 ^A	55.0	109.0	60.0	55.0	109.0	60.0	73.0	106.0	70.0	85.0	109.0	60.0
1/2	15	65.0	111.0	60.0	65.0	111.0	60.0	85.0	106.0	70.0	85.0	111.0	60.0
3/4	20	80.0	112.0	70.0	80.0	112.0	70.0	95.0	108.0	70.0	95.0	112.0	70.0
1	25	90.0	142.0	90.0	90.0	142.0	90.0	108.0	119.0	80.0	110.0	142.0	90.0
1 1/4	32	105.0	150.0	90.0	105.0	150.0	90.0	120.0	142.0	90.0	130.0	150.0	90.0
1 1/2	40	120.0	171.0	100.0	120.0	171.0	100.0	135.0	155.0	90.0	150.0	171.0	100.0
2	50	140.0	189.0	115.0	140.0	189.0	115.0	155.0	186.0	115.0	180.0	189.0	115.0
2 1/2	65	180.0	253.0	180.0	180.0	253.0	180.0				210.0	253.0	180.0
3	80	200.0	280.0	225.0	200.0	280.0	225.0				240.0	280.0	225.0
ボデー	SCS13A			SCS14A			SCS13A			SCS13A			
ボンネット	SCS13A			SCS14A			SUS304:10 ^A -20 ^A SCS13A:25 ^A -50 ^A			SCS13A			
ステム	SUS304+ハードCrめっき			SUS316+ハードCrめっき			SUS304+ハードCrめっき			SUS304+ハードCrめっき			
ジスク	SUS304/SCS13A			SUS316/SCS14A			SUS304			SUS304/SCS13A			
パッキン	膨張黒鉛+PTFE編組			膨張黒鉛+PTFE編組			膨張黒鉛+PTFE編組			膨張黒鉛+PTFE編組			
ガスケット	非石棉シート			非石棉シート			膨張黒鉛+PTFE編組			非石棉シート			
ハンドル	ZDC:3/8 ^B -3/4 ^B ADC12:1 ^B -2 ^B FCD400-15-2 1/2 ^B -3 ^B			ZDC:3/8 ^B -3/4 ^B ADC12:1 ^B -2 ^B FCD400-15-2 1/2 ^B -3 ^B			ZDC:10 ^A -20 ^A ADC12:25 ^A -50 ^A			ZDC:10 ^A -20 ^A ADC12:25 ^A -50 ^A FCD400-15-65 ^A -80 ^A			
接続形状	ねじ込み:JIS B0203			ねじ込み:JIS B0203			フランジ:JIS B2220 10K			フランジ:JIS B2220 10K			
最高許容圧力	圧力-温度基準:SUS46			圧力-温度基準:SUS46			圧力-温度基準:SUS46			圧力-温度基準:SUS46			
備考	・JV8-1適合:1/2 ^B -2 ^B ・RoHS指令相当品			・JV8-1適合:1/2 ^B -2 ^B ・RoHS指令相当品			RoHS指令相当品			・JV8-1相当:15 ^A -50 ^A ・RoHS指令相当品:10 ^A -50 ^A			