



Types and Specifications

Name and type		Universal tee (barb fitting)						Nipple (barb fitting)			
											
Model		UTF3.2-M3	UTF4-M3	UTF3.2	UTF4	UTF5	UTF6	NBF3.2	NBF4	NBF5	NBF6
Port size		M3×0.5 (male thread)		M5×0.8 (male thread)						—	
Applicable tube O.D.×I.D.mm		3.2×2.4	4×2.5	3.2×2.4	4×2.5	5×3	6×4	3.2×2.4	4×2.5	5×3	6×4
Effective area mm ²		0.6		1.6		1.7		1.6		2.1	3.6
Operating temperature range °C [°F]		0~60 [32~140]									
Material		Body :Brass (nickel plated) Thread :Stainless steel		Brass (nickel plated)				Brass (nickel plated)			
Mass g [oz.]		2.0 [0.071]		5.6 [0.198]	5.7 [0.201]	6.0 [0.212]	6.4 [0.226]	0.25 [0.0088]	0.5 [0.018]	0.75 [0.0265]	1.25 [0.0441]
Remark	Attachment	With 2 gaskets						—			
	Sales unit	1 pack (5 pcs.)						1 pack (10 pcs.)			