

IMPACT RATCHET

Main Features

1. Impact clutch mechanism.
2. 2.5 times faster.
(As compared to other Kuken ratchet wrench.)
3. Reducing the reaction force after the screw sitting.



■ 3/8" (9.5mm) SQ. DR.

KRI-10

Drive Size	3/8 in.	9.5 mm
Bolt Capacity	3/8 in.	10.0 mm
Free Speed	500 r.p.m.	
Maximum Torque	22 ft-lb	30 Nm
Length (w/o socket)	6-7/8 in.	174.0 mm
Weight (w/o socket)	1.4 lbs.	0.65 kg
Air Consumption (normal)	8.8 c.f.m.	0.25 m ³ /min
Hose Size	1/4 in.	6.5 mm

*Performance figures are at 0.62MPa(Pe)(90P.S.I.)air pressure.



NARROW WRENCH

KNAW-22H

Bolt Capacity	7/8 in.	22.0 mm
Free Speed	1,800 r.p.m.	
Maximum Torque	480 ft-lb	650 Nm
Length (w/o socket)	15-1/8 in.	384.0 mm
Width (w/o socket)	3-7/8 in.	97.0 mm
Width (Gear Case)	1-9/16 in.	38.5 mm
Weight (w/o socket)	15.2 lbs.	6.9 kg
Air Consumption (normal)	20.5 c.f.m.	0.58 m ³ /min
Hose Size	1/2 in.	12.7 mm

※ Performance figures are at 0.62MPa(Pe)(90P.S.I.)air pressure.

Main Features

1. N-Type Clutch
2. High power : 650 Nm
3. For crank pulley bolts
4. For narrow places
5. Various sockets & adapters

