

























IMG	CODE	MATERIAL	DIMENSIONS	FLUX DENSITY	ATTRACTIVE FORCE
	NRD0002	Neodymium	Φ15mmXΦ6mmX2mm Dia	355mT	0.486kgf
	NRD0003	Neodymium	Φ15mmXΦ10mmX4mm Dia	303mT	0.53kgf
	NRD0004	Neodymium	Φ23mmXΦ19mmX6mm Dia	256.2mT	0.788kgf
	NRD0005	Neodymium	Φ23.3mmXΦ19.3mmX6mm Dia	255.4mT	0.794kgf
	NRD0006	Neodymium	Φ23.7mmXΦ19.7mmX6mm Dia	254.5mT	0.801kgf
	NRD0007	Neodymium	Φ24mmXΦ4mmX6mm Dia	538mT	3.62kgf
	NRD0008	Neodymium	Φ24mmXΦ20mmX6mm Dia	253.8mT	0.807kgf
	NA0001	Neodymium	R25mmXr10mmXH20mmXA90rad	495.9mT	0.016kgf
	NA0002	Neodymium	R22.5mmXr17.5mmXH30mmXA60rad	515.5mT	0.005kgf
	NA0003	Neodymium	R29mmXr14mmXH15mmXA60rad	469.2mT	0.012kgf
	NAD0004	Neodymium	R9.5mmXr8mmXL4mmXA25rad Dia	289.4mT	0.199kgf
	NAD0001	Neodymium	R15mmXr10mmXL40mmXA90rad Dia	293.5mT	5.76kgf
	NAD0006	Neodymium	R15mmXr10mmXL80mmXA180rad Dia	181mT	0.817kgf
	NAD0003	Neodymium	R22mmXr18mmXL10mmXA45rad Dia	344.2mT	1.66kgf
	NAD0005	Neodymium	R41mmXr5mmXL8.5mmXA90rad Dia	542.5mT	7.94kgf
	NS0070	Neodymium	1mmX1mmX1mm	186.9mT	0.041kgf
	NS0352	Neodymium	1mmX1mmX5mm	213.1mT	0.05kgf
	NS0205	Neodymium	2mmX2mmX1mm	245.7mT	0.097kgf
	NS0421	Neodymium	2.2mmX2.2mmX1mm	242mT	0.105kgf
	NS0207	Neodymium	2mmX2mmX1.5mm	295.2mT	0.14kgf
	NS0064	Neodymium	2mmX2mmX2mm	321.3mT	0.167kgf
	NS0208	Neodymium	2mmX2mmX4mm	354.8mT	0.203kgf
	NS0001	Neodymium	2.4mmX2.4mmX1.8mm	324.4mT	0.202kgf
	NS0422	Neodymium	2.7mmX2.7mmX1mm	236.2mT	0.138kgf