

























| IMG  | CODE    | MATERIAL  | DIMENSIONS         | FLUX DENSITY | ATTRACTIVE FORCE |
|--|---------|-----------|--------------------|--------------|------------------|
|    | NS0417  | Neodymium | 72mmX72mmX24mm     | 306.6mT      | 103kgf           |
|    | NS0375  | Neodymium | 75mmX10mmX3mm      | 207.5mT      | 15kgf            |
|    | NS0314  | Neodymium | 75mmX30mmX3mm      | 80.9mT       | 9.09kgf          |
|    | NS0443  | Neodymium | 80mmX15mmX5mm      | 228mT        | 25.2kgf          |
|    | NS0444  | Neodymium | 80mmX40mmX40mm     | 475.1mT      | 111kgf           |
|    | NS0316  | Neodymium | 85mmX14mmX2mm      | 107.3mT      | 8.43kgf          |
|    | NS0275  | Neodymium | 100mmX20mmX7mm     | 237.5mT      | 44.1kgf          |
|    | NS0319  | Neodymium | 100mmX40mmX10mm    | 190.6mT      | 58.5kgf          |
|    | NS0411  | Neodymium | 100mmX100mmX20mm   | 202.1mT      | 148kgf           |
|   | NS0418  | Neodymium | 120mmX35mmX25mm    | 385.3mT      | 112kgf           |
|  | NS0341  | Neodymium | 139mmX8mmX8mm      | 422.3mT      | 54.7kgf          |
|  | NS0327  | Neodymium | 150mmX8mmX8mm      | 422.2mT      | 61.1kgf          |
|  | NS0445  | Neodymium | 150mmX15mmX5mm     | 224.9mT      | 56.6kgf          |
|  | NS0331  | Neodymium | 200mmX15mmX5mm     | 224.3mT      | 81.9kgf          |
|  | NSC0071 | Neodymium | 4mmX4mmX1.5mm/M1.4 | 266.6mT      | 0.304kgf         |
|  | NSC0017 | Neodymium | 5mmX5mmX2mm/M1.4   | 292.7mT      | 0.484kgf         |
|  | NSC0018 | Neodymium | 5mmX5mmX3mm/M1.4   | 367.4mT      | 0.734kgf         |
|  | NSC0019 | Neodymium | 6mmX6mmX2mm/M1.4   | 267.3mT      | 0.657kgf         |
|  | NSC0020 | Neodymium | 6mmX6mmX3mm/M1.4   | 347.3mT      | 0.879kgf         |
|  | NSC0021 | Neodymium | 6mmX6mmX4mm/M1.4   | 398.8mT      | 1.15kgf          |
|  | NSC0022 | Neodymium | 8mmX8mmX3mm/M2     | 302.3mT      | 1.22kgf          |
|  | NSC0023 | Neodymium | 8mmX8mmX4mm/M2     | 361.2mT      | 1.56kgf          |
|  | NSC0024 | Neodymium | 8mmX8mmX5mm/M2     | 403.6mT      | 1.95kgf          |
|  | NSC0045 | Neodymium | 8mmX8mmX6mm/M2     | 434mT        | 2.25kgf          |