


## Depth Gage

### Depth Micrometer SERIES 329, 129 — Interchangeable Rod Type

#### Interchangeable rod (Optional Accessories)

(Check and adjust the origin point before measurement)



Range (mm)	0 - 25	25 - 50	50 - 75	75 - 100	100 - 125	125 - 150	150 - 175	175 - 200	200 - 225	225 - 250	250 - 275	275 - 300
Analog models	<b>Order No.</b> 983501	983503	983505	983507	983509	983511	983525	983527	983529	983531	983533	983535
	L (mm)	104	129	154	179	204	229	254	279	304	329	379
Digimatic models	<b>Order No.</b> 983505	983507	983509	983511	983525	983527	983529	983531	983533	983535	981781	981782
	L (mm)	154	179	204	229	254	279	304	329	354	379	429

Range (in)	0 - 1	1 - 2	2 - 3	3 - 4	4 - 5	5 - 6	6 - 7	7 - 8	8 - 9	9 - 10	10 - 11	11 - 12
Analog models	<b>Order No.</b> 983502	983504	983506	983508	983510	983512	983526	983528	983530	983532	983534	983536
	L (mm)	104.3	129.7	155.1	180.5	205.9	231.3	256.7	282.1	307.5	332.9	358.3
Digimatic models	<b>Order No.</b> 983506	983508	983510	983512	983526	983528	983530	983532	983534	983536	981783	981784
	L (mm)	155.1	180.5	205.9	231.3	256.7	282.1	307.5	332.9	358.3	383.7	434.5

## DIMENSIONS

