



FMA フェイスミルアーバ

FACE MILL ARBOR (TYPE-A)



BT30

| CODE | FIG | φd | L | D | H | K | W | C | C1 | G |
|--------------------|-----|-------|----|----|----|---|------|---|----|---------|
| BT30-FMA25.4 - 45 | 1 | 25.4 | 45 | 50 | 22 | 5 | 9.5 | - | 33 | MBA-M12 |
| | | | 75 | | | | | | | |
| BT30-FMA31.75 - 45 | 3 | 31.75 | 45 | 60 | 30 | 7 | 12.7 | - | 40 | MBA-M16 |

BT40

| CODE | FIG | φd | L | D | H | K | W | C | C1 | G |
|--------------------|-----|-------|-----|----|----|---|------|----|----|---------|
| BT40-FMA25.4 - 45 | 1 | 25.4 | 45 | 50 | 22 | 5 | 9.5 | - | 33 | MBA-M12 |
| | | | 75 | | | | | | | |
| | | | 100 | | | | | | | |
| | | | 105 | | | | | | | |
| | | | 125 | | | | | | | |
| BT40-FMA25.4 - 150 | 2 | 25.4 | 150 | 50 | 22 | 5 | 9.5 | 60 | 33 | MBA-M12 |
| | | | 150 | | | | | | | |
| BT40-FMA31.75 - 75 | 1 | 31.75 | 75 | 60 | 30 | 7 | 12.7 | - | 40 | MBA-M16 |
| | | | 100 | | | | | | | |
| | | | 125 | | | | | | | |
| | | | 150 | | | | | | | |
| BT40-FMA38.1 - 75 | 3 | 38.1 | 75 | 80 | 34 | 9 | 15.9 | - | 50 | MBA-M20 |
| | | | 100 | | | | | | | |

BT50

| CODE | FIG | φd | L | D | H | K | W | C | C1 | G |
|---------------------|-----|--------|-----|--------|----|------|-------|---|----|---------|
| BT50-FMA25.4 - 90 | 2 | 25.4 | 90 | 50 | 22 | 5 | 9.5 | - | 33 | MBA-M12 |
| | | | 150 | | | | | | | |
| | | | 200 | | | | | | | |
| | | | 250 | | | | | | | |
| | | | 300 | | | | | | | |
| | | | 350 | | | | | | | |
| BT50-FMA31.75 - 45 | 2 | 31.75 | 45 | 60 | 30 | 7 | 12.7 | - | 40 | MBA-M16 |
| | | | 75 | | | | | | | |
| | | | 105 | | | | | | | |
| | | | 150 | | | | | | | |
| | | | 200 | | | | | | | |
| | | | 250 | | | | | | | |
| | | | 300 | | | | | | | |
| | | | 350 | | | | | | | |
| | | | 70 | | | | | | | |
| 80 | | | | | | | | | | |
| BT50-FMA38.1 - 45 | 1 | 38.1 | 45 | 80 | 34 | 9 | 15.9 | - | 50 | MBA-M20 |
| | | | 75 | | | | | | | |
| | | | 105 | | | | | | | |
| | | | 150 | | | | | | | |
| | | | 200 | | | | | | | |
| | | | 250 | | | | | | | |
| | | | 300 | | | | | | | |
| | | | 350 | | | | | | | |
| BT50-FMA50.8 - 45 | 1 | 50.8 | 45 | 100 | 36 | 10 | 19.05 | - | 65 | MBA-M24 |
| | | | 75 | | | | | | | |
| | | | 105 | | | | | | | |
| | | | 150 | | | | | | | |
| | | | 200 | | | | | | | |
| | | | 250 | | | | | | | |
| BT50-FMA47.625 - 75 | 4 | 47.625 | 75 | 128.57 | 38 | 12.5 | 25.4 | - | - | HCB-M16 |
| | | | 100 | | | | | | | |
| | | | 150 | | | | | | | |
| | | | 200 | | | | | | | |

■特殊サイズも注文により製作いたします。 Special size is available upon request.

FMA47.625 → FMB60 変換スリーブ

| CODE |
|-----------------|
| φ 47.625 × φ 60 |