

# Thin pad / PNG

## How to order

① ②  
**PNG - 101 - N**

① Pad diameter (mm)

101	φ31	114	φ17
102	φ25	116	φ18
103	φ25	117	φ17.6
104	φ24.8	121	φ31
106	φ25	122	φ34
107	φ49	123	φ15
108	φ40	125	φ24
109	φ17	130A	φ20
110	φ23	130B	φ20
111	φ25	131	φ25
112	φ27		

② Pad rubber material

N	NBR (Nitrile rubber)(101/116/122/130A/130B/131)
S	Silicone rubber(101/114/116/117/121/130A/130B/131)
U	Urethane rubber(104/110/116/125/130B)
F	Fluorine rubber(130B)
NR	Natural rubber(101/102/103/104/106/107/108/109/110/111/112/114/123)

Note) Please consult with us for other material.

## Pad standard specifications

Symbol	Material	Hardness (Hs)	Ambient temperature	Color
N	NBR (Nitrile rubber)	A55/S	-26 ~ 120°C	Black
S	Silicone rubber	A55/S	-60 ~ 250°C	white
U	Urethane rubber	A55/S	-20 ~ 75°C	Blue
F	Fluorine rubber	A70/S	-10 ~ 230°C	Black with white dot
NR	Natural rubber	A40/S	-60 ~ 80°C	Light brown

## Dimensions

Unit : mm <inch>

