

●電気ドリル、ボール盤など三爪チャックで使用し  
やすいシャンクのドリルです。

This drill is used by Jacobs chucks at drill stand and power drills.



6形 (1/4) 6Type

LIST 574

オーダー方法

NOS 直径 -4

直径 Dc	溝長 ℓ	全長 L	シャンク径 Ds	シャンク長 ℓs	在庫 Stock	参考価格 Price
7.0	35	75	6.5	25	●	1,190
7.5	35	75	6.5	25	●	1,320
8.0	35	75	6.5	25	●	1,490
8.5	35	75	6.5	25	●	1,720
9.0	35	75	6.5	25	●	1,900
9.5	35	75	6.5	25	●	2,080
10.0	48	95	6.5	30	●	2,200
10.5	48	95	6.5	30	●	2,400
11.0	48	95	6.5	30	●	2,590
11.5	48	95	6.5	30	●	2,830
12.0	48	95	6.5	30	●	3,000
12.5	48	95	6.5	30	●	3,260
13.0	48	95	6.5	30	●	3,370


10形 (3/8) 10Type

LIST 576

オーダー方法

NOS 直径 -8

直径 Dc	溝長 ℓ	全長 L	シャンク径 Ds	シャンク長 ℓs	在庫 Stock	参考価格 Price
10.5	65	120	9.5	35	●	2,550
11.0	65	120	9.5	35	●	2,720
11.5	65	120	9.5	35	●	2,940
12.0	65	120	9.5	35	●	3,150
12.5	65	120	9.5	35	●	3,260
13.0	65	120	9.5	35	●	3,400
13.5	65	120	9.5	35	●	3,610
14.0	65	120	9.5	35	●	3,830
14.5	65	120	9.5	35	●	4,140
15.0	65	120	9.5	35	●	4,360
15.5	65	120	9.5	35	●	4,580
16.0	65	120	9.5	35	●	4,880



13形 (1/2) 13Type

LIST 578

オーダー方法

NOS 直径 -2

単位 (Unit) : mm / 円 (¥)

直径 Dc	溝長 ℓ	全長 L	シャンク径 Ds	シャンク長 ℓs	在庫 Stock	参考価格 Price
13.1	74	134	12.65	40	□	-
13.2	74	134	12.65	40	□	-
13.3	74	134	12.65	40	□	-
13.4	74	134	12.65	40	□	-
13.5	74	134	12.65	40	●	3,760
13.6	74	134	12.65	40	□	-
13.7	74	134	12.65	40	□	-
13.8	74	134	12.65	40	□	-
13.9	74	134	12.65	40	□	-
14.0	74	134	12.65	40	●	4,060
14.1	74	134	12.65	40	□	-
14.2	74	134	12.65	40	□	-
14.3	74	134	12.65	40	□	-
14.4	74	134	12.65	40	□	-
14.5	74	134	12.65	40	●	4,330
14.6	74	134	12.65	40	□	-
14.7	74	134	12.65	40	□	-
14.8	74	134	12.65	40	□	-
14.9	74	134	12.65	40	□	-
15.0	74	134	12.65	40	●	4,580
15.1	74	134	12.65	40	□	-
15.2	74	134	12.65	40	□	-
15.3	74	134	12.65	40	□	-
15.4	74	134	12.65	40	□	-
15.5	74	134	12.65	40	●	4,840
15.6	74	134	12.65	40	□	-
15.7	74	134	12.65	40	□	-
15.8	74	134	12.65	40	□	-
15.9	74	134	12.65	40	□	-
16.0	74	134	12.65	40	●	5,140
16.1	74	134	12.65	40	□	-
16.2	74	134	12.65	40	□	-
16.3	74	134	12.65	40	□	-
16.4	74	134	12.65	40	□	-
16.5	74	134	12.65	40	●	5,420
16.6	74	134	12.65	40	□	-
16.7	74	134	12.65	40	□	-
16.8	74	134	12.65	40	□	-
16.9	74	134	12.65	40	□	-
17.0	74	134	12.65	40	●	5,640
17.1	74	134	12.65	40	□	-
17.2	74	134	12.65	40	□	-
17.3	74	134	12.65	40	□	-
17.4	74	134	12.65	40	□	-
17.5	74	134	12.65	40	●	5,940
17.6	74	134	12.65	40	□	-
17.7	74	134	12.65	40	□	-
17.8	74	134	12.65	40	□	-
17.9	74	134	12.65	40	□	-
18.0	74	134	12.65	40	●	6,130
18.1	74	134	12.65	40	□	-
18.2	74	134	12.65	40	□	-
18.3	74	134	12.65	40	□	-
18.4	74	134	12.65	40	□	-
18.5	74	134	12.65	40	●	6,460
18.6	74	134	12.65	40	□	-
18.7	74	134	12.65	40	□	-
18.8	74	134	12.65	40	□	-
18.9	74	134	12.65	40	□	-
19.0	74	134	12.65	40	●	6,780

シャンク部のV溝は円周上に3溝あります。これはスリップ止め用の溝で10形、13形に施してあります。保護リングも10形、13形についてあります。(6形にはV溝および保護リングはありません。)包装数量は6形(1/4)のみ5本、その他は1本です。