

# LSDP



## 鉄工用ロングドリル

Long Drills for Steels



●もっとも広い用途で使用される汎用のロングドリルです。

This is general HSS long drills for deep holes.



直径 6.0 未満 直径 6.0 以上  
S 形シンニング

オーダ方法

LSDP 直径 × 全長

単位 (Unit) : mm

直径 Dc	溝長 ℓ	全長 L	JAN コード 4991893	包装 本数
2.0	40	100	121025	1
2.0	60	150	121346	1
2.5	50	100	121032	1
2.5	60	150	121353	1
2.8	75	150	127836	1
3.0	50	100	121049	1
3.0	75	150	121056	1
3.2	75	150	121063	1
3.3	75	150	121070	1
3.5	75	150	121087	1
3.5	100	200	121094	1
3.7	75	150	121100	1
3.8	75	150	121117	1
4.0	75	150	121124	1
4.0	100	200	121131	1
4.2	75	150	121148	1
4.2	100	200	121155	1
4.5	75	150	121162	1
4.5	100	200	121179	1
4.8	75	150	127843	1
5.0	75	150	121186	1
5.0	100	200	121193	1
5.0	120	250	121209	1
5.5	100	150	128918	1
5.5	100	200	121216	1
6.0	100	150	121223	1
6.0	100	200	121230	1
6.0	120	250	121247	1
6.5	100	200	121254	1
7.0	100	200	121261	1
7.0	120	250	121278	1
8.0	100	200	121285	1
8.0	120	250	121292	1
9.0	100	200	121308	1
9.0	120	250	121315	1
10.0	100	200	121322	1
10.0	120	250	121339	1

# NOSP


## 電ドル用ノスドリル

Noss Drills



●電気ドリルやボール盤で使いやすいドリルです。

This drill is easy to use with electric drills and drill presses.



オーダ方法

NOSP 直径 — 柄記号

単位 (Unit) : mm

NOSP-4

直径 Dc	溝長 ℓ	全長 L	シャンク径 Ds	シャンク長 ℓs	JAN コード 4991893	包装 本数
7.0	35	75	6.5	25	047356	1
7.5	35	75	6.5	25	047363	1
8.0	35	75	6.5	25	047370	1
8.5	35	75	6.5	25	047387	1
9.0	35	75	6.5	25	047394	1
9.5	35	75	6.5	25	047400	1
10.0	48	95	6.5	25	047417	1
10.5	48	95	6.5	25	047424	1
11.0	48	95	6.5	25	047431	1
11.5	48	95	6.5	25	047448	1
12.0	48	95	6.5	25	047455	1
12.5	48	95	6.5	25	047462	1
13.0	48	95	6.5	25	047479	1

NOSP-8

直径 Dc	溝長 ℓ	全長 L	シャンク径 Ds	シャンク長 ℓs	JAN コード 4991893	包装 本数
10.5	65	120	9.5	35	047486	1
11.0	65	120	9.5	35	047493	1
11.5	65	120	9.5	35	047509	1
12.0	65	120	9.5	35	047516	1
12.5	65	120	9.5	35	047523	1
13.0	65	120	9.5	35	047530	1
13.5	65	120	9.5	35	047547	1
14.0	65	120	9.5	35	047554	1
14.5	65	120	9.5	35	047561	1
15.0	65	120	9.5	35	047578	1
15.5	65	120	9.5	35	047585	1
16.0	65	120	9.5	35	047592	1

NOSP-2

直径 Dc	溝長 ℓ	全長 L	シャンク径 Ds	シャンク長 ℓs	JAN コード 4991893	包装 本数
13.5	74	134	12.65	40	047608	1
14.0	74	134	12.65	40	047615	1
14.5	74	134	12.65	40	047622	1
15.0	74	134	12.65	40	047639	1
15.5	74	134	12.65	40	047646	1
16.0	74	134	12.65	40	047653	1
16.5	74	134	12.65	40	047660	1
17.0	74	134	12.65	40	047677	1
17.5	74	134	12.65	40	047684	1
18.0	74	134	12.65	40	047691	1
18.5	74	134	12.65	40	047707	1
19.0	74	134	12.65	40	047714	1
19.5	74	134	12.65	40	047721	1
20.0	74	134	12.65	40	047738	1
20.5	74	134	12.65	40	047745	1
21.0	74	134	12.65	40	047752	1
21.5	74	134	12.65	40	047769	1
22.0	74	134	12.65	40	047776	1