



工具材料 コーティング 直径許容差 先端角 ねじれ角 直径範囲

- 鋼、ステンレス鋼、アルミに適した汎用のコーティングオイルホールドリルです。
- 深い穴加工に最適です。

This is general coated taper shank long drills with oil-hole, and has rich variation of flute.



オーダ方法

GLTDOH 直径 × 全長

直径5.0~10.0  
在庫品限り

単位 (Unit) : mm

直径 Dc	全長 L	溝長 ℓ	シャンク MT No.	給油方式 Coolant Supply	在庫 Stock
5.0	300	200	2	2・3	□
5.0	350	230			
5.0	400	280			
5.0	450	300			
5.0	500	350			
5.5	300	200			
5.5	350	230			
5.5	400	280			
6.0	300	200			
6.0	350	230			
6.0	400	280			
6.0	450	300			
6.0	500	350			
6.5	300	200			
6.5	350	230			
6.5	400	280			
7.0	300	200			
7.0	350	230			
7.0	400	280			
7.0	450	300			
7.0	500	350			
7.5	300	200			
7.5	350	230			
7.5	400	280			
8.0	300	200			
8.0	350	230			
8.0	400	280			
8.0	450	300			
8.0	500	350			
8.0	600	400			
8.5	300	200			
8.5	350	230			
8.5	400	280			
9.0	300	200			
9.0	350	230			
9.0	400	280			
9.0	450	300			
9.0	500	350			
9.0	600	400			
9.5	300	200			
9.5	350	230			
9.5	400	280			
10.0	300	200			
10.0	350	230			
10.0	400	280			
10.0	450	300			
10.0	500	350			
10.0	600	400			
10.0	800	600			
10.5	300	200			
10.5	350	230			
10.5	400	280			
11.0	300	200			
11.0	350	230			
11.0	400	280			
11.0	450	300			
11.0	500	350			
11.0	600	400			
11.0	800	600			
11.5	300	200			
11.5	350	230			
11.5	400	280			
12.0	300	200			
12.0	350	230			

直径 Dc	全長 L	溝長 ℓ	シャンク MT No.	給油方式 Coolant Supply	在庫 Stock
12.0	400	280	2	2・3	□
12.0	450	300			
12.0	500	350			
12.0	600	400			
12.0	800	600			
12.5	300	200			
12.5	350	230			
12.5	400	280			
12.5	450	300			
12.5	500	350			
12.5	600	400			
13.0	300	200			
13.0	350	230			
13.0	400	280			
13.0	450	300			
13.0	500	350			
13.0	600	400			
13.0	800	600			
13.5	300	200			
13.5	350	230			
13.5	400	280			
13.5	450	300			
13.5	500	350			
13.5	600	400			
14.0	300	200			
14.0	350	230			
14.0	400	280			
14.0	450	300			
14.0	500	350			
14.0	600	400			
14.0	800	600			
14.5	350	230			
14.5	400	260			
14.5	500	350			
14.5	600	400			
15.0	350	220			
15.0	400	260			
15.0	500	350			
15.0	600	400			
15.0	800	600			
15.5	350	220			
15.5	400	260			
15.5	500	350			
15.5	600	400			
16.0	350	220			
16.0	400	260			
16.0	450	300			
16.0	500	350			
16.0	600	400			
16.0	800	600			
16.5	350	220			
16.5	400	260			
16.5	500	350			
16.5	600	400			
17.0	350	220			
17.0	400	260			
17.0	450	300			
17.0	500	350			
17.0	600	400			
17.0	800	600			
17.5	350	220			
17.5	400	260			
17.5	500	350			
17.5	600	400			

□は特定代理店在庫品です。  
Available for Japan customers only.

油穴付きドリルです。給油方式 1・2・3 は 1形、2形、3形兼用です。給油方式の説明は G-44 を参照ください。首部とシャンク部後端タング部に止めねじが挿入されています。それぞれを取り外すことにより 1形、3形に転用できます。