

NK-1900 Female Union x Male Threaded Type

DN: 6mm(1/8") ~ 50mm(2")

Length: 200mm ~ 10M

*For any other specifications, please contact us.



①	Tube	Stainless Steel
②	Braid	Stainless Steel
③	Collar	Stainless Steel
④	Union	Carbon Steel, Stainless Steel
⑤	Gasket	Non Asbestos
⑥	Ring	Stainless Steel
⑦	Nipple	Carbon Steel, Stainless Steel

NK-2000 Slim Union Type

DN: 6mm(1/8") ~ 50mm(2")

Length: 200mm ~ 10M

*For any other specifications, please contact us.



NK-2000MM : Both male thread ends (Metal Touch Seal)

NK-2000FF : Both female thread ends (Metal Touch Seal)

NK-2000MF : Male x Female ends (Metal Touch Seal)

①	Tube	Stainless Steel
②	Braid	Stainless Steel
③	Ring	Stainless Steel
④	Sleeve	Carbon Steel, Stainless Steel
⑤	Nut	Carbon Steel, Stainless Steel
⑥	Male Union	Carbon Steel, Stainless Steel
⑦	Female Union	Carbon Steel, Stainless Steel

NK-3400 Light Union Type

DN: 6mm(1/8") ~ 25mm(1")

Length: 200mm ~ 10M

*For any other specifications, please contact us.



NK-3400MM : Both male thread ends (Metal Touch Seal)

NK-3400FF : Both female thread ends (Metal Touch Seal)

NK-3400MF : Male x Female ends (Metal Touch Seal)

①	Tube	Stainless Steel
②	Braid	Stainless Steel
③	Base Block	Carbon Steel, Stainless Steel
④	Ring	Carbon Steel, Stainless Steel
⑤	Nut	Carbon Steel, Stainless Steel
⑥	Male Union	Carbon Steel, Stainless Steel
⑦	Female Union	Carbon Steel, Stainless Steel