


## NK-FJ-A Male Threaded Type

DN: 6mm(1/8") ~ 50mm(2")  
Length: 250mm ~ 10M

NK-FJS-A/Straight Tube



NK-FJP-A/Spiral Corrugated Tube



NK-FJS-A/Straight Tube

① Nipple	Carbon Steel, Stainless Steel
② Ring	Stainless Steel
③ Tube	PTFE
④ Braid	Stainless Steel
⑤ Guard Spring	Stainless Steel



NK-FJP-A/Spiral Corrugated Tube

① Nipple	Carbon Steel, Stainless Steel
② Ring	Stainless Steel
③ Tube	PTFE
④ Braid	Stainless Steel

## NK-FJ-B Male Union Type

DN: 6mm(1/8") ~ 50mm(2")  
Length: 250mm ~ 10M

NK-FJS-B/Straight Tube



NK-FJP-B/ Spiral Corrugated Tube



NK-FJS-B/Straight Tube

① Nipple	Carbon Steel, Stainless Steel
② Nut	Stainless Steel
③ Sleeve	Stainless Steel
④ Ring	Stainless Steel
⑤ Tube	PTFE
⑥ Braid	Stainless Steel
⑦ Guard Spring	Stainless Steel



NK-FJP-B/ Spiral Corrugated Tube

① Nipple	Carbon Steel, Stainless Steel
② Nut	Carbon Steel, Stainless Steel
③ Sleeve	Stainless Steel
④ Ring	Stainless Steel
⑤ Tube	PTFE
⑥ Braid	Stainless Steel