





■ HIGH PRECISION LEVEL LEVELNIC SERIES

Body Picture	 Built-in wireless	 Built-in wireless		
Model Name · Model No.	Levelnic DL-S4W series	Levelnic DL-S2W series	Levelnic DL-S3 series	Levelnic DL-S3L
Features	<ul style="list-style-type: none"> ● Display of high precision 0.001mm/m ● Switchable wire / wireless 	<ul style="list-style-type: none"> ● Display of high precision 0.001mm/m ● Wireless data output 	<ul style="list-style-type: none"> ● Display of high precision 0.001mm/m ● Wired data output (RS-232C) 	<ul style="list-style-type: none"> ● Levelnic DL-S3 with L-type base ● Magnetic base enables Z-axis measurement in addition to X-axis and Y-axis. ● Super strong magnet
Resolution	0.001mm/m · 0.0001°	0.001mm/m · 0.0001°	0.001mm/m · 0.0001°	0.001mm/m · 0.0001°
Measuring Range	± 5.00mm/m · ± 0.286°	± 5.000mm/m · ± 0.2865°	± 5.00mm/m · ± 0.286°	± 5.00mm/m · ± 0.286°
Wireless Data Output	○	○	△: Optional ⇒ P131	△: Optional ⇒ P131
Wired Data Output	○	×	○	○
Display Measured Value	○	×	○	○
Refer to	125	128	126	127

Body Picture				
Model Name · Model No.	Levelnic DL-m3 series	Levelnic DL-m3LS	Levelnic DL-m1 series	Separate System / Levelnic Cable
Features	<ul style="list-style-type: none"> ● Display of 0.01mm/m ● Lightweight, compact and easy-to-carry ● Wired data output (RS-232C) 	<ul style="list-style-type: none"> ● Levelnic DL-m3 on L-type base ● Magnetic base enables Z-axis measurement in addition to X-axis and Y-axis. 	<ul style="list-style-type: none"> ● Display of 0.01mm/m ● Lightweight, compact and easy-to-carry 	<ul style="list-style-type: none"> ● Display of high precision 0.001mm/m ● Suitable for leveling of higher place and larger machinery
Resolution	0.01mm/m	0.01mm/m	0.01mm/m	0.001mm/m · 0.0001°
Measuring Range	± 5.00mm/m	± 5.00mm/m	± 5.00mm/m	± 5.000mm/m · ± 0.2865°
Wireless Data Output	△: Optional ⇒ P131	△: Optional ⇒ P131	×	△: Optional ⇒ P131
Wired Data Output	○	○	×	○
Display Measured Value	○	○	○	Levelnic Display
Refer to	129	130	129	134

Body Picture			<ul style="list-style-type: none"> ● Wireless adapter ● Levelnic display ● Software for flatness and straightness measurement ● Carrying case other options are available.
Model Name · Model No.	Levelnic DL-S1	Levelnic EL-01A	  <p>Please refer to P127 ~ P139</p>
Features	<ul style="list-style-type: none"> ● Display of 0.01mm/m ● Wide measuring range of ± 9.99mm/m 	<ul style="list-style-type: none"> ● Display of 0.01mm/m Analog level ● Connectable to analog recorder 	
Resolution	0.01mm/m	± 0.2mm/m (1division 0.01mm/m) ± 1mm/m (1division 0.05mm/m) ± 2mm/m (1division 0.1mm/m)	
Measuring Range	± 9.99mm/m		
Wireless Data Output	×	×	
Wired Data Output	×	○: Analog output	
Display Measured Value	○	○	
Refer to	135	136	