

### TYPICAL SWITCH ORDERING EXAMPLE

**UB** **1** **5** **SK** **G** **03** **5C** — **CC**

Poles	
1	SPDT
2	DPDT

Mounting Types	
<b>PCB Mounting</b>	
SK	Square
RK	Rectangular
<b>* Snap-in Mounting</b>	
KK	Square
NK	Rectangular
NBK	Rectangular with Side Barriers
* Standard with Solder Lug terminals	

Circuits	
5	ON (ON)
( ) = Momentary	
6	ON ON
Alternate Action with Latchdown	

Contacts & Ratings	
W	Silver Rated 5A @ 125/250V AC
G	Gold Rated 0.4VA max @ 28V AC/DC max

Terminals	
01	Solder Lug* (for Snap-in Mounting)
03	Straight PC

LEDs	
<b>Bright LED</b>	
5C	Red
5D	Amber
5F	Green
<b>Super Bright LED</b>	
6B	White
6F	Green
6G	Blue
Available with Square only	
<b>Nonilluminated</b>	
N	Nonilluminated

Cap Types & Colors			
<b>Full Face Illuminated Cap for Bright LED</b>			
Lens/Diffuser Colors			
CB	Red/White	FF	Green/Green
CC	Red/Red	*FJ	Green/Clear
*CJ	Red/Clear	JB	Clear/White
DB	Amber/White	JC	Clear/Red
DD	Amber/Amber	JD	Clear/Amber
*DJ	Amber/Clear	JF	Clear/Green
FB	Green/White	*JJ	Clear/Clear
AB	Square & Rectangular Spot Illuminated Black Cap with White Window		
* Not available with Rectangular cap			
<b>Full Face Illuminated Cap for Super Bright LED</b>			
JB	Clear Lens/White Diffuser		
AB	Spot Illuminated Black Cap with White Window		
For Square only; see cap detail page			
<b>Nonilluminated Cap Colors</b>			
A	Black	E	Yellow
B	White	F	Green
C	Red	G	Blue

\* Wire harness & cable assemblies offered only in Americas

**IMPORTANT:**

Switches are supplied without UL, cULus & CSA marking unless specified. **UL, cULus & CSA recognized only when ordered with marking on the switch.** Specific models, ratings, & ordering instructions are noted on General Specifications page.

### DESCRIPTION FOR TYPICAL ORDERING EXAMPLE

**UB15SKG035C-CC**

