



FlexScan® EV2430

24.1" (61.1 cm) LCD Monitor



The Perfect Office All-Rounder

Tireless Eyes

To prevent eye fatigue, a brightness sensor called Auto EcoView detects the changes in the ambient brightness that occur throughout the day and automatically adjusts the screen to the ideal brightness level. Auto EcoView cuts power by almost 40% compared to operating the monitor at maximum brightness.



Paper Mode Reduces Eye Fatigue

Paper Mode is a preset color mode that simulates the look of printed paper and helps prevent eyestrain when reading documents by reducing the amount of blue light emitted from the monitor.



A Clear View from All Angles

The FlexScan EV2430 has 178° horizontal and vertical viewing angles which makes it suitable for most business use.



Flicker-Free Images

Due to the way brightness is controlled on LED backlights, a small number of people perceive flicker on their screen which causes eye fatigue. The FlexScan EV2430 utilizes a hybrid solution to regulate brightness and make flicker unperceivable without any drawbacks like compromising color stability.



Preset Modes for Optimum Viewing

Five preset modes (including two with user adjustable settings) ensure you always get the right setting for any application. You can switch modes with just the touch of a button.