



19" LCD Monitor

FlexScan® S1934



19" Square Monitor with IPS Panel for Offices and Control Rooms

Optimized Brightness with Auto EcoView

The Auto EcoView function is a sensor on the front of the monitor that measures ambient light and optimizes the screen's brightness to a level akin to viewing a sheet of paper under typical office lighting conditions. Since the screen is never too bright, eye strain is reduced while power consumption is cut by up to 50% compared to operating the monitor with Auto EcoView turned off and set to the default factory brightness of 100%.



Three Inputs Including DisplayPort

DisplayPort, DVI-D 24-pin, and D-Sub mini 15-pin inputs are included for connection with various graphics boards.



DisplayPort DVI-D 24-pin D-Sub mini 15-pin

Reduced Blue Light

A preset mode called "Paper" adjusts the brightness, contrast ratio, and color temperature to simulate those of printed paper. Paper mode significantly reduces the amount of blue light emitted from the screen for more comfortable viewing.

