



# Needle Scalers



**Lightweight:  
820g**

**Compact  
Body: 26mm  
diameter**

**Excellent  
Scaling  
Power**

NPK offers the lightest and most compact needle scalers. Low vibration for improved safety and comfort.

### Applications

- \* Removal of flux or spatter after welding
- \* Removal of rust or mill scale from a steel plate
- \* Removal of paint & other hardened industrial coatings
- \* Cleaning & prepping of any flat or contoured surface



**3 mm x 7 pcs**

**NHR-00**

Needle  $\phi$  3x125L  
code#17202091



**2 mm x 13 pcs**

**NHR-00-02**

Needle  $\phi$  2x125L  
code#17202092



Model	Code	Needles	Blow/min min <sup>-1</sup>	Piston dia mm	Piston stroke mm	Length mm	Weight kg	Air inlet thread Rc	Hose size mm	Average air consumption m <sup>3</sup> /min
NHR-00	30470	3mm x 7 x 125L	6,500	14	12	216	0.82	1/4	9.5	0.2
NHR-00-02	30469	2mm x 13 x 125L	6,500	14	12	216	0.82	1/4	9.5	0.2



### Applications

- \* Removal of flux or spatter after welding
- \* Removal of rust or mill scale from a steel plate
- \* Removal of paint & other hardened industrial coatings
- \* Cleaning & prepping of any flat or contoured surface



A slim and ergonomic grip and powerful performance.

**NHR-20**

Model	Code	Needles	Blow/min min <sup>-1</sup>	Piston dia mm	Piston stroke mm	Length mm	Weight kg	Air inlet thread Rc	Hose size mm	Average air consumption m <sup>3</sup> /min
NHR-20	30453	3mm x 12 x 180L	4,000	20	27.5	245	2.1	1/4	9.5	0.2