

屋内用
片扉 IP2XD
両扉 IP2XC

ライトベージュ塗装
LB色(SY71)
白塗工F25-70B

クリーム塗装
クリーム色(2,SY91)
白塗工F22-90B

フカサ 250mm

単位/mm

納期区分		木製基板付		納期区分		鉄製基板付		標準価格 円	一梱入数	扉形式	外形寸法			取付基板寸法		有効フカサ		製品質量 kg	
LB色	C色	品名記号	LB色	C色	品名記号	ヨコ	タテ				フカサ	ヨコ	タテ	Bタイプ	Sタイプ	Bタイプ	Sタイプ	Bタイプ	Sタイプ
◎	◎	B25-84-1	◎	◎	S25-84-1		39,000	1	片扉	800	400	250	720	320	218	231	21.5	23.7	
◎	◎	B25-84-2	◎	◎	S25-84-2		42,500	1	両扉	"	"	"	"	"	"*	"*	22.7	24.9	
◎	◎	B25-85-1	◎	◎	S25-85-1		44,500	1	片扉	"	500	"	"	420	"	"	25.1	27.9	
◎	◎	B25-85-2	◎	◎	S25-85-2		48,500	1	両扉	"	"	"	"	"	"*	"*	26.3	29.1	
◎	◎	B25-86-1	◎	◎	S25-86-1		49,500	1	片扉	"	600	"	"	520	"	"	28.7	32.2	
◎	◎	B25-86-2	◎	◎	S25-86-2		53,000	1	両扉	"	"	"	"	"	"*	"*	30.0	33.4	
◎	◎	B25-87-1	◎	◎	S25-87-1		51,500	1	片扉	"	700	"	"	620	"	"	32.4	36.4	
③	③	B25-87-2	◎	◎	S25-87-2		55,000	1	両扉	"	"	"	"	"	"*	"*	33.7	37.7	
◎	◎	B25-88-1	◎	◎	S25-88-1		53,500	1	片扉	"	800	"	"	720	"	"	36.0	40.6	
◎	◎	B25-88-2	◎	◎	S25-88-2		57,000	1	両扉	"	"	"	"	"	"*	"*	37.3	42.0	
◎	◎	B25-89-1	◎	◎	S25-89-1		63,000	1	片扉	"	900	"	"	820	"	"	39.6	44.8	
◎	◎	B25-89-2	◎	◎	S25-89-2		66,500	1	両扉	"	"	"	"	"	"*	"*	41.0	46.3	
◎	◎	B25-810-1	◎	◎	S25-810-1		68,500	1	片扉	"	1,000	"	"	920	"	225	43.3	49.2	
◎	◎	B25-810-2	◎	◎	S25-810-2		72,000	1	両扉	"	"	"	"	"	"*	"*	45.0	50.9	
◎	◎	B25-812-1	◎	◎	S25-812-1		75,500	1	片扉	"	1,200	"	"	1,120	"	"	50.5	57.7	
◎	◎	B25-812-2	◎	◎	S25-812-2		79,000	1	両扉	"	"	"	"	"	"*	"*	52.4	59.5	
◎	◎	B25-814-1	◎	◎	S25-814-1		83,500	1	片扉	"	1,400	"	"	1,320	"	"	62.7	71.1	
◎	③	B25-814-2	◎	◎	S25-814-2		87,000	1	両扉	"	"	"	"	"	"*	"*	64.7	73.1	
◎	◎	B25-816-1	◎	◎	S25-816-1		97,000	1	片扉	"	1,600	"	"	1,520	"	"	70.5	80.1	
③	③	B25-816-2	◎	◎	S25-816-2		101,000	1	両扉	"	"	"	"	"	"*	"*	72.7	82.3	
◎	◎	B25-97-2	◎	◎	S25-97-2		64,000	1	両扉	900	700	250	820	620	218*	231*	36.9	41.5	
◎	◎	B25-106-2	◎	◎	S25-106-2		62,000	1	両扉	1,000	600	250	920	520	218*	225*	35.9	40.2	
◎	◎	B25-108-2	◎	◎	S25-108-2		72,000	1	"	"	800	"	"	720	"*	"*	44.6	50.5	
◎	◎	B25-1010-2	◎	◎	S25-1010-2		83,500	1	"	"	1,000	"	"	920	"*	"*	53.7	61.7	
◎	◎	B25-1012-2	◎	◎	S25-1012-2		90,000	1	"	"	1,200	"	"	1,120	"*	"*	62.4	72.1	
◎	◎	B25-1014-2	◎	◎	S25-1014-2		109,000	1	"	"	1,400	"	"	1,320	"*	"*	76.5	87.8	
◎	◎	B25-1016-2	◎	◎	S25-1016-2		122,000	1	"	"	1,600	"	"	1,520	"*	"*	85.9	98.8	
◎	◎	B25-1018-2	◎	◎	S25-1018-2		161,000	1	"	"	1,800	"	"	1,720	"*	"*	106.5	121.1	
◎	◎	B25-1020-2	◎	◎	S25-1020-2		179,000	1	"	"	2,000	"	"	1,920	"*	"*	117.2	133.4	
◎	◎	B25-128-2	◎	◎	S25-128-2		83,500	1	両扉	1,200	800	250	1,120	720	218*	225*	51.8	59.0	
◎	◎	B25-1210-2	◎	◎	S25-1210-2		93,500	1	"	"	1,000	"	"	920	"*	"*	62.3	72.0	
◎	◎	B25-1212-2	◎	◎	S25-1212-2		111,000	1	"	"	1,200	"	"	1,120	"*	"*	72.4	84.1	
◎	◎	B25-1214-2	◎	◎	S25-1214-2		129,000	1	"	"	1,400	"	"	1,320	"*	"*	88.2	101.8	
◎	◎	B25-1216-2	◎	◎	S25-1216-2		144,000	1	"	"	1,600	"	"	1,520	210*	225*	100.2	115.8	
◎	◎	B25-1218-2	◎	◎	S25-1218-2		189,000	1	"	"	1,800	"	"	1,720	"*	"*	123.0	140.5	
◎	◎	B25-1220-2	◎	◎	S25-1220-2		206,000	1	"	"	2,000	"	"	1,920	"*	"*	135.2	154.7	
◎	◎	B25-1410-2	◎	◎	S25-1410-2		107,000	1	両扉	1,400	1,000	250	1,320	920	218*	225*	75.6	86.9	
③	③	B25-1416-2	◎	◎	S25-1416-2		156,000	1	"	"	1,600	"	"	1,520	210*	"*	131.6	131.8	

★両扉の合せ部の有効フカサは上記有効フカサより23mm引いた寸法となります。

フカサ 300mm

◎	◎	B30-45	◎	◎	S30-45		30,000	1	片扉	400	500	300	320	420	268	281	16.0	17.3
◎	◎	B30-46	◎	◎	S30-46		34,000	1	"	"	600	"	"	520	"	"	18.3	19.9
◎	◎	B30-55	◎	◎	S30-55		35,000	1	片扉	500	500	300	420	420	268	281	18.7	20.4
◎	◎	B30-56	◎	◎	S30-56		39,000	1	"	"	600	"	"	520	"	"	21.4	23.4
◎	◎	B30-57	◎	◎	S30-57		42,500	1	"	"	700	"	"	620	"	"	24.1	26.5
◎	◎	B30-58	◎	◎	S30-58		46,500	1	"	"	800	"	"	720	"	"	26.8	29.6
◎	◎	B30-59	◎	◎	S30-59		51,500	1	"	"	900	"	"	820	"	"	29.4	32.6
◎	◎	B30-65	◎	◎	S30-65		39,000	1	片扉	600	500	300	520	420	268	281	21.4	23.5
◎	◎	B30-66	◎	◎	S30-66		42,500	1	"	"	600	"	"	520	"	"	24.4	26.9
◎	◎	B30-67	◎	◎	S30-67		46,500	1	"	"	700	"	"	620	"	"	27.5	30.4
◎	◎	B30-68	◎	◎	S30-68		51,500	1	"	"	800	"	"	720	"	"	30.5	33.9
◎	◎	B30-610	◎	◎	S30-610		56,500	1	"	"	1,000	"	"	920	"	275	36.7	41.0

◎代理店様在庫品 ◎物流センター在庫品 ①③⑤⑦標準品(納期別)

上記品名記号はライトベージュ塗装です。
クリーム塗装にてご注文の際は品名記号の末尾にCを付けてご用命ください。
価格は同価格です。[例]B25-84-1→B25-84-1Cとなります。