

# ステンレス製ねじ込み管継手

MADE OF STAINLESS STEEL

SCS13A (SUS304)

品名	ブッシング		六角異径ニップル		異径ソケット			径違いチー	
記号	B		SRN		RS			RT	
形状									
呼び径 (B)	L7	S4	L8	S5	d3	d4	L9	A9	A10
1/4 x 1/8	17	17	33	14	19	15	25	18	18
3/8 x 1/8	18	21	34	17	23	15	28		
3/8 x 1/4	18	21	35	17	23	19	28	20	22
1/2 x 1/8	21	26							
1/2 x 1/4	21	26	39	22	27	19	34	24	24
1/2 x 3/8	21	26	39	22	27	23	34	26	25
3/4 x 1/8	24	34							
3/4 x 1/4	24	34						25	28
3/4 x 3/8	24	34	42	27	33	23	38	28	28
3/4 x 1/2	24	34	45	27	33	27	38	29	30
1 x 1/4	27	38							
1 x 3/8	27	38						30	31
1 x 1/2	27	38	48	35	41	27	42	32	33
1 x 3/4	27	38	50	35	41	33	42	34	35
1 1/4 x 3/8	30	46							
1 1/4 x 1/2	30	46			50	27	48	34	37
1 1/4 x 3/4	30	46	52	43	50	33	48	38	40
1 1/4 x 1	30	46	54	43	50	41	48	40	42
1 1/2 x 1/2	32	54							
1 1/2 x 3/4	32	54			56	33	52	38	43
1 1/2 x 1	32	54	57	49	56	41	52	41	45
1 1/2 x 1 1/4	32	54	59	49	56	50	52	45	48
2 x 3/4	36	63							
2 x 1	36	63	61	61	69	41	58	44	51
2 x 1 1/4	36	63	63	61	69	50	58	48	54
2 x 1 1/2	36	63	64	61	69	56	58	52	55
2 1/2 x 1	39	80							
2 1/2 x 1 1/4	39	80			86	50	65		
2 1/2 x 1 1/2	39	80			86	56	65		
2 1/2 x 2	39	80			86	69	65		
3 x 1 1/4	44	95							
3 x 1 1/2	44	95			99	56	72		
3 x 2	44	95			99	69	72		
3 x 2 1/2	44	95			99	86	72		
4 x 1 1/2	51	120							
4 x 2	51	120							
4 x 2 1/2	51	120							
4 x 3	51	120							

単位：mm



NAGOYA Co.,LTD