

呼び寸法 $b \times h \times 300$

平行キー材 S45C

呼び寸法	b	h	c
3 X 3 X 300	3	3	0.16~0.25
4 X 4 X 300	4	4	0.16~0.25
5 X 5 X 300	5	5	0.25~0.40
6 X 6 X 300	6	6	0.25~0.40
7 X 7 X 300	7	7	0.25~0.40
8 X 7 X 300	8	7	0.25~0.40
10 X 8 X 300	10	8	0.40~0.60
12 X 8 X 300	12	8	0.40~0.60
14 X 9 X 300	14	9	0.40~0.60
15 X 10 X 300	15	10	0.40~0.60
16 X 10 X 300	16	10	0.40~0.60
18 X 11 X 300	18	11	0.40~0.60
20 X 12 X 300	20	12	0.60~0.80
22 X 14 X 300	22	14	0.60~0.80
25 X 14 X 300	25	14	0.60~0.80
28 X 16 X 300	28	16	0.60~0.80
32 X 18 X 300	32	18	0.60~0.80
36 X 20 X 300	36	20	1.00~1.20
40 X 22 X 300	40	22	1.00~1.20
45 X 25 X 300	45	25	1.00~1.20
50 X 28 X 300	50	28	1.00~1.20
56 X 32 X 300	56	32	1.60~2.00

平行キー材 S45C-Q

呼び寸法	b	h	c
5 X 5 X 300	5	5	0.25~0.40
6 X 6 X 300	6	6	0.25~0.40
7 X 7 X 300	7	7	0.25~0.40
8 X 7 X 300	8	7	0.25~0.40
10 X 8 X 300	10	8	0.25~0.40
12 X 8 X 300	12	8	0.40~0.60
14 X 9 X 300	14	9	0.40~0.60
16 X 10 X 300	16	10	0.40~0.60
18 X 11 X 300	18	11	0.40~0.60
20 X 12 X 300	20	12	0.60~0.80
22 X 14 X 300	22	14	0.60~0.80
25 X 14 X 300	25	14	0.60~0.80
28 X 16 X 300	28	16	0.60~0.80
32 X 18 X 300	32	18	0.60~0.80
36 X 20 X 300	36	20	1.00~1.20
40 X 22 X 300	40	22	1.00~1.20
45 X 25 X 300	45	25	1.00~1.20
50 X 28 X 300	50	28	1.00~1.20

平行キー材 SUS304

呼び寸法	b	h	c
3 X 3 X 300	3	3	0.16~0.25
4 X 4 X 300	4	4	0.16~0.25
5 X 5 X 300	5	5	0.25~0.40
6 X 6 X 300	6	6	0.25~0.40
7 X 7 X 300	7	7	0.25~0.40
8 X 7 X 300	8	7	0.25~0.40
10 X 8 X 300	10	8	0.40~0.60
12 X 8 X 300	12	8	0.40~0.60
14 X 9 X 300	14	9	0.40~0.60
15 X 10 X 300	15	10	0.40~0.60
16 X 10 X 300	16	10	0.40~0.60
18 X 11 X 300	18	11	0.40~0.60
20 X 12 X 300	20	12	0.60~0.80
22 X 14 X 300	22	14	0.60~0.80
25 X 14 X 300	25	14	0.60~0.80