

# Air Clean Unit

# ZN-A


CSM\_ZN-A\_DS\_E\_2\_2

The ZN series is even thinner and sports improved air volume. These products enable cleaning that is both fast and flexible.



- Three sizes are available to match various sizes of clean booths.






 Be sure to read "Safety Precautions" on page 4.

For the most recent information on models that have been certified for safety standards, refer to your OMRON website.

## Ordering Information

### Air Clean Units

#### Air Clean Units

Appearance	Application	Power supply	Model
	250 × 250 mm	24 VDC	ZN-A2502D *
	410 × 410 mm		ZN-A4105D *
	610 × 610 mm		ZN-A6112
			ZN-A6112P *


\*This type is equipped with a clog detection function.

#### Accessories

	Application	Model	Qty.
Replacement HEPA Filters	For 250 × 250 mm	ZN9-AHP25	1
	For 410 × 410 mm	ZN9-AHP41	1
	For 610 × 610 mm	ZN9-AHP61	1
Replacement Pre-filters	For 250 × 250 mm	ZN9-APF25	2
	For 410 × 410 mm	ZN9-APF41	1
	For 610 × 610 mm	ZN9-APF61	1

### Ionizers Units

#### Ionizers

Appearance	Application	Power supply	Model
	250 × 250 mm	Supplied from the Air Clean Unit.	ZN-J25A
	410 × 410 mm		ZN-J41A

#### Accessories

	Model	Qty.
Replacement Discharge Needles	ZN9-JH04	4 per pack

#### Single-sided Connector Cables (for DC power supply or I/O connection)

Cable length	Model	Qty.
2 m	ZN9-JC02	1